

## Copper SIMpull XHHW-2®

Power Cable 600 or 1000 Volt Single Conductor Copper, Cross Linked Polyethylene (XLPE) with SIMpull technology for easier pulling.



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) with SIMpull technology

### APPLICATIONS AND FEATURES:

#### APPLICATION

Southwire® SIMpull XHHW-2® copper conductors are primarily used in conduit, cable tray or other recognized raceways for services, feeders, and branch circuit wiring, as specified in the National Electrical Code. SIMpull XHHW-2® copper conductors may be used in wet or dry locations at temperatures not to exceed 90°C. Voltage rating for XHHW-2 conductors is 600 volts or 1000 volts for all sizes. Suitable for use in Health Care Facilities per Section 517.160 of the National Electrical Code where a dielectric constant of less than 3.5 maybe specified. This cable is designed to be installed without the application of pulling lubricant.

Note: Simpull technology on Sizes # 8 and Larger. Non-Simpull technology on #14, #12, #10.

#### FEATURES

- Sunlight resistant - #8 AWG and larger
- Gasoline and Oil Resistant II - #8 AWG and larger
- CT Rated - 1/0 AWG and Larger
- FT1 - #8 AWG and larger
- FT4 - 350 kcmil and larger
- SIS - Sizes 14 through 8 AWG
- -40°C cold bend - #8 AWG and larger
- RoHS Compliant

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202/FT4 Flame Test (70,000 BTU/hr) 350kcmil and Larger



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: March 21, 2024, 12:21 p.m. UTC REVISION: 1.000.018

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- Federal Specification A-A-59544
- NMX-J-451-ANCE Thermoset insulated wires and cables
- NOM-063-SCFI Electrical Products – Conductors – Safety Requirements

SAMPLE PRINT LEGEND:

14 AWG thru 10 AWG  
SOUTHWIRE E30117 (UL) XX AWG (XXXmm2) CU TYPE XHHW-2 600V/1000V OR SIS 600 VOLTS NOM-ANCE

350 kcmil and Larger  
{SQFTG} SOUTHWIRE® {NOLUBE}® {SIMPULL}® E30117 {UL} TYPE XHHW-2 XXX KCMIL (XXX{MM2}) CU 600V/1000V SR  
FOR CT USE GRII PRII FT4 - {NOM}-ANCE LS - PAT WWW.PATENTSW.COM

Table 1 – Weights and Measurements

| Cond. Size | Cond. Number | Strand Count   | Diameter Over Conductor | Insul. Thickness | Approx. OD | Copper Weight | Approx. Weight |
|------------|--------------|----------------|-------------------------|------------------|------------|---------------|----------------|
| AWG/Kcmil  |              | No. of Strands | inch                    | mil              | inch       | lb/1000ft     | lb/1000ft      |
| 3          | 1            | 7              | 0.252                   | 45               | 0.348      | 162           | 184            |

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

| Cond. Size | Cond. Number | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity At 60°C | Allowable Ampacity At 75°C | Allowable Ampacity At 90°C |
|------------|--------------|--------------------|------------------|----------------------|----------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| AWG/Kcmil  |              | inch               | lb               | Ω/1000ft             | Ω/1000ft             | Ω/1000ft                   | Amp                        | Amp                        | Amp                        |
| 3          | 1            | 1.3                | 420              | 0.205                | 0.246                | 0.047                      | 85                         | 100                        | 115                        |

\* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.  
\* Inductive Reactance is based on non-ferrous conduit with one diameter spacing.

## Stock Code Colors and Standard Package

| Size       | Package                                | Black                                                                             | Red                                                                               | Blue                                                                              | White                                                                             | Brown                                                                              | Orange                                                                              | Yellow                                                                              | Gray                                                                                | Green                                                                               |
|------------|----------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|            |                                        |  |  |  |  |  |  |  |  |  |
| 14 (7)     | Reel: 2500'<br>Spool: 500'             | 112920                                                                            | 370932                                                                            | 370940                                                                            | 370924                                                                            | 370981                                                                             | 370973                                                                              | 370957                                                                              | 371005                                                                              | 370965                                                                              |
| 12 (Solid) | Reel: 2500'<br>Spool: 500'             | 550220                                                                            | 550222                                                                            | 550224                                                                            | 550221                                                                            | 550227                                                                             | 550226                                                                              | 550225                                                                              |                                                                                     | 550223                                                                              |
| 12 (7)     | Reel: 2500'<br>Spool: 500'             | 112938                                                                            | 371039                                                                            | 371047                                                                            | 371021                                                                            | 371088                                                                             | 371070                                                                              | 371054                                                                              | 371104                                                                              | 371062                                                                              |
| 10 (Solid) | Reel: 2500'<br>Spool: 500'             | 137240                                                                            | 550213                                                                            | 550215                                                                            | 550212                                                                            | 550218                                                                             | 550217                                                                              | 550216                                                                              |                                                                                     | 550214                                                                              |
| 10 (7)     | Reel: 2500'<br>Spool: 500'             | 112946                                                                            | 371138                                                                            | 371146                                                                            | 371120                                                                            | 371187                                                                             | 371179                                                                              | 371153                                                                              | 371203                                                                              | 371161                                                                              |
| 8          | Reel: 1000'/2500'/5000'<br>Spool: 500' | 112953                                                                            | 952713                                                                            | 588683                                                                            | 952721                                                                            | 553060                                                                             | 550361                                                                              | 553062                                                                              | 553063                                                                              | 952739                                                                              |
| 6          | Reel: 1000'/2500'/5000'<br>Spool: 500' | 112961                                                                            | 952705                                                                            | 959916                                                                            | 678607                                                                            | 683383                                                                             | 683391                                                                              | 553067                                                                              | 553068                                                                              | 553230                                                                              |
| 4          | Reel: 1000'/2500'/5000'<br>Spool: 500' | 112979                                                                            | 952697                                                                            | 553846                                                                            | 678599                                                                            | 553847                                                                             | 553848                                                                              | 553849                                                                              | 553850                                                                              | 558627                                                                              |
| 3          | Reel: 1000'<br>Spool: 500'             | 267278                                                                            |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |                                                                                     | 890469                                                                              |
| 2          | Reel: 1000'/2500'/5000'<br>Spool: 500' | 112987                                                                            | 218115                                                                            | 553087                                                                            | 218107                                                                            | 553088                                                                             | 553089                                                                              | 553090                                                                              | 553091                                                                              | 474122                                                                              |
| 1          | Reel: 1000'/2500'/5000'<br>Spool: 500' | 112995                                                                            | 550761                                                                            | 550762                                                                            | 550808                                                                            | 553854                                                                             | 553855                                                                              | 553856                                                                              | 553857                                                                              | 550766                                                                              |
| 1/0        | Reel: 1000'/2500'/5000'<br>Spool: 500' | 113001                                                                            | 553860                                                                            | 553861                                                                            | 553858                                                                            | 553863                                                                             | 553864                                                                              | 553865                                                                              | 553866                                                                              | 553862                                                                              |
| 2/0        | Reel: 1000'/2500'/5000'<br>Spool: 500' | 113019                                                                            | 553871                                                                            | 553872                                                                            | 553870                                                                            | 553873                                                                             | 553874                                                                              | 553876                                                                              | 553877                                                                              | 552070                                                                              |
| 3/0        | Reel: 1000'/2500'/5000'<br>Spool: 500' | 113027                                                                            | 553881                                                                            | 553882                                                                            | 553880                                                                            | 553885                                                                             | 553886                                                                              | 553887                                                                              | 553888                                                                              | 553884                                                                              |
| 4/0        | Reel: 1000'/2500'/5000'<br>Spool: 500' | 113035                                                                            | 553078                                                                            | 553079                                                                            | 553077                                                                            | 553080                                                                             | 553082                                                                              | 553083                                                                              | 553084                                                                              | 552071                                                                              |
| 250        | Reel: 1000'/2500'/5000'<br>Spool: 500' | 113043                                                                            | 553893                                                                            | 553894                                                                            | 553892                                                                            | 553896                                                                             | 553897                                                                              | 553898                                                                              | 553899                                                                              | 553895                                                                              |
| 300        | Spool: 500'                            | 113050                                                                            |                                                                                   |                                                                                   |                                                                                   | 561129                                                                             | 561130                                                                              | 561131                                                                              | 584039                                                                              |                                                                                     |
| 350        | Reel: 1000'/2500'                      | 113068                                                                            | 553903                                                                            | 553904                                                                            | 553902                                                                            | 553906                                                                             | 553907                                                                              | 553908                                                                              | 553910                                                                              | 553905                                                                              |
| 400        | Reel: 1000'/2500'<br>Spool: 500'       | 113076                                                                            | 561701                                                                            | 561702                                                                            | 561132                                                                            | 561111                                                                             | 561112                                                                              | 561113                                                                              | 561703                                                                              | 558666                                                                              |
| 500        | Reel: 1000'/2500'<br>Spool: 500'       | 113084                                                                            | 550369                                                                            | 550261                                                                            | 553071                                                                            | 550260                                                                             | 550262                                                                              | 550259                                                                              | 553074                                                                              | 553072                                                                              |
| 600        | Reel: 1000'/2500'<br>Spool: 500'       | 113092                                                                            | 553914                                                                            | 553915                                                                            | 553913                                                                            | 553918                                                                             | 553919                                                                              | 553920                                                                              | 553921                                                                              | 553916                                                                              |
| 700        | N/A                                    | 586272                                                                            |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |                                                                                     |                                                                                     |
| 750        | Reel: 2500'                            | 113100                                                                            | 553927                                                                            | 553930                                                                            | 553926                                                                            | 553930                                                                             | 553931                                                                              | 553932                                                                              | 553934                                                                              | 553929                                                                              |
| 1000       | N/A                                    | 113134                                                                            |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |                                                                                     |                                                                                     |

