

Broadband Coax RG59 and 18/2 Round




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Copper braid shielded
4. **Signal:** 2/C #18 Black, Red
5. **Jacket:** Polyvinyl Chloride PVC.

APPLICATIONS AND FEATURES:

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID

SPECIFICATIONS:

- Sunlight Resistance

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® 99979 E57497 18 AWG/2C 20 AWG 1/C RG 59/U (UL) TYPE CL2P



Table 1 – Physical and Electrical Data

| Stock Number | Cable Type | Rating | Cond. Size | Cond. Number | Cond. Type | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Shield Type | Application |
|--------------|------------|--------|-------------------------|--------------|------------|---------------|------------------|------------------|-------------|----------------|--------------|---|
| | | | AWG | No. | | strands | mil | mil | inch | lb /1000ft | | |
| RG59 | | | | | | | | | | | | |
| 92094 | RG59 | CM CL2 | Coax 20 AWG + 2x 18 AWG | 3 | BC + SBC | Solid | 61 | 30 | 0.226x0.364 | 54 | Copper Braid | CATV - Combo RG59 Coaxial Plus 2/C 18AWG Under One Jacket |
| 99979 | RG59 | CL2P | Coax 20 AWG + 2x 18 AWG | 3 | BC + SBC | Solid | 55 | 30 | 0.226x0.364 | 54 | Copper Braid | CATV - Combo RG59 Coaxial Plus 1 Pair/ 18AWG Under One Jacket |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

