

CU 600/1000V XLPE Insulation PVC Jacket XHHW-2. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type TC-ER Power Cable 600 or 1000 Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Polyvinyl Chloride (PVC) Jacket with 1 Copper Ground (Bare or Insulated). CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
- Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8. (When present, cable conductor sizes 8 & 6 AWG have an insulated green ground)
- Filler:** Paper filler (cable size 8 & 6 uses Polypropylene filler)
- Binder:** Polyester flat thread binder tape for cable sizes larger than 2 AWG
- Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 or 1000 Volt Type TC-ER power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10. Sunlight Resistant - For Direct Burial - Silicone Free

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Jan. 24, 2024, 6:11 p.m. UTC REVISION: 1.000.007

SAMPLE PRINT LEGEND:

Bare Ground: {SQFTG} SOUTHWIRE® {UL} XX AWG (X.XX{mm2}) 3/C TYPE TC-ER XHHW-2 CDRS 90°C JACKET SUNLIGHT RESISTANT DIRECT BURIAL 600V or 1000V {NOM}-ANCE XHHW-2 CT FT4 SR 600V 90C

Green Ground: {SQFTG} SOUTHWIRE® {UL} XX AWG (X.XX{mm2}) CU 3/C TYPE TC-ER XHHW-2 CDRS GW 1 X X AWG CU GREEN INSULATED 90°C JACKET SUNLIGHT RESISTANT DIRECT BURIAL 600V or 1000V {NOM}-ANCE XHHW-2 CT FT4 SR 600V 90C

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil		No. of Strands	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft
555196◇	8	3	7	0.141	45	- x -	60	0.627	154	283
480590◇	8	3	7	0.141	45	1 x 10 GG	60	0.688	186	327
555195	6	3	7	0.177	45	- x -	60	0.704	245	386
480608◇	6	3	7	0.177	45	1 x 8 GG	60	0.782	297	466
480616◇	4	3	7	0.225	45	1 x 8	60	0.806	441	612
480624◇	2	3	7	0.282	45	1 x 6	80	0.982	702	927
480632◇	1	3	19	0.322	55	1 x 6	80	1.106	864	1142
480640◇	1/0	3	19	0.361	55	1 x 6	80	1.200	1069	1417
480657◇	2/0	3	19	0.405	55	1 x 6	80	1.295	1326	1723
480665◇	3/0	3	19	0.456	55	1 x 4	80	1.399	1699	2065
480673◇	4/0	3	19	0.512	55	1 x 4	80	1.494	2109	2502
480681◇	250	3	37	0.558	65	1 x 4	80	1.619	2469	2940
672206	350	3	37	0.661	65	1 x 1	115	1.897	3535	4322
480707◇	350	3	37	0.661	65	1 x 3	115	1.910	3438	4127
588013	350	3	37	0.661	65	1 x 3/0	115	2.093	3797	4602
480715	400	3	37	0.705	65	1 x 3	115	2.014	3906	4756
480723◇	500	3	37	0.789	65	1 x 2	115	2.167	4884	5701
890148	500	3	37	0.789	65	1 x 1/0	115	2.167	5007	5929
583697	500	3	37	0.789	65	1 x 2/0	115	2.274	5092	6099
593173	600	3	61	0.865	80	1 x 3/0	115	2.417	6136	7286
665766	600	3	61	0.865	80	1 x 1/0	115	2.417	5942	7038
890388◇	600	3	61	0.865	80	1 x 2	115	2.417	5820	6812
665766◇	600	3	61	0.865	80	1 x 2	110	2.436	5814	6950
665768	600	3	61	0.865	80	1 x 400	115	2.503	6860	7994
672210	600	3	61	0.865	80	1 x 250	115	2.578	6392	7594
589359	750	3	61	0.968	80	1 x 4/0	115	2.631	7676	8996
554410	750	3	61	0.968	80	1 x 1	115	2.631	7277	8597

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Jan. 24, 2024, 6:11 p.m. UTC REVISION: 1.000.007

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 60°C	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
555196◇	8	3	2.5	396	0.653	0.786	0.052	40	50	55
480590◇	8	3	2.8	396	0.653	0.786	0.052	40	50	55
555195	6	3	2.8	629	0.411	0.495	0.051	55	65	75
480608◇	6	3	3.1	629	0.411	0.495	0.051	55	65	75
480616◇	4	3	3.2	1001	0.258	0.310	0.048	70	85	95
480624◇	2	3	3.9	1592	0.162	0.195	0.045	95	115	130
480632◇	1	3	5.5	2008	0.128	0.154	0.046	110	130	145
480640◇	1/0	3	6.0	2534	0.102	0.122	0.044	125	150	170
480657◇	2/0	3	6.5	3194	0.081	0.097	0.043	145	175	195
480665◇	3/0	3	7.0	4027	0.064	0.078	0.042	165	200	225
480673◇	4/0	3	7.5	5078	0.051	0.062	0.041	195	230	260
480681◇	250	3	8.1	6000	0.043	0.053	0.041	215	255	290
672206	350	3	9.5	8400	0.031	0.039	0.040	260	310	350
480707◇	350	3	9.6	8400	0.031	0.039	0.040	260	310	350
588013	350	3	12.6	8400	0.031	0.039	0.040	260	310	350
480715	400	3	12.1	9600	0.027	0.035	0.040	280	335	380
480723◇	500	3	13.0	12000	0.022	0.029	0.039	320	380	430
890148	500	3	13.0	12000	0.022	0.029	0.039	320	380	430
583697	500	3	13.6	12000	0.022	0.029	0.039	320	380	430
593173	600	3	14.5	14400	0.018	0.025	0.039	350	420	475
665766	600	3	14.5	14400	0.018	0.025	0.039	350	420	475
890388◇	600	3	14.5	14400	0.018	0.025	0.039	350	420	475
665766◇	600	3	14.6	14400	0.018	0.025	0.039	350	420	475
665768	600	3	15.0	14400	0.018	0.025	0.039	350	420	475
672210	600	3	15.5	14400	0.018	0.025	0.039	350	420	475
589359	750	3	15.8	18000	0.014	0.022	0.038	400	475	535
554410	750	3	15.8	18000	0.014	0.022	0.038	400	475	535

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

