

CU Compact 15kV NLEPR Insulation 100% IL Black SIM-PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Compact Copper, 175 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, SIMpull® Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded per ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 175 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -25°C for cold bend and cold impact and marked with "LTDD" when CSA listed or dual UL/CSA listed. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.002

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE SIMpull® POWER CABLE {UL} XXX KCMIL CPT CU 175 MILS NL-EPR 15KV 100% INS LEVEL 25%TS MV-105 SUN. RES. {NESC} PAT www.patentSW.com

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch	inch
TBA	2	7	0.268	0.656	0.716	80	0.896	219	526	530	10.7	2.5
TBA	1	19	0.298	0.686	0.746	80	0.926	273	596	669	11.1	3.0
TBA	1/0	19	0.336	0.724	0.784	80	0.964	341	684	844	11.5	3.0
TBA	2/0	19	0.376	0.764	0.824	80	1.004	427	791	1064	12.0	3.0
TBA	3/0	19	0.422	0.810	0.870	80	1.050	535	922	1342	12.6	3.0
TBA	4/0	19	0.474	0.862	0.922	80	1.102	671	1085	1692	13.2	3.5
TBA	250	37	0.520	0.916	0.976	80	1.156	791	1237	2000	13.8	3.5
TBA	350	37	0.615	1.011	1.071	80	1.251	1101	1597	2800	15.0	3.5
583511	500	35	0.735	1.162	1.222	80	1.402	1641	2206	4000	16.8	4.0
TBA	750	61	0.908	1.314	1.374	80	1.554	2343	3007	6000	18.6	4.5
TBA	1000	61	1.060	1.466	1.526	110	1.766	3116	3964	8000	21.1	5.0

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.046	0.049	0.574 + j0.464	0.204 + j0.049	2249	155/165	195/215
1	0.128	0.162	0.043	0.048	0.533 + j0.447	0.162 + j0.046	2342	175/185	225/250
1/0	0.102	0.128	0.040	0.046	0.499 + j0.428	0.128 + j0.044	2459	200/215	260/290
2/0	0.081	0.102	0.036	0.044	0.472 + j0.410	0.102 + j0.043	2584	230/245	300/335
3/0	0.064	0.081	0.033	0.043	0.450 + j0.390	0.081 + j0.041	2726	260/275	345/385
4/0	0.051	0.065	0.031	0.041	0.432 + j0.368	0.066 + j0.040	2887	295/315	400/445
250	0.043	0.056	0.029	0.040	0.420 + j0.348	0.057 + j0.039	3054	325/345	445/495
350	0.031	0.041	0.025	0.038	0.398 + j0.316	0.042 + j0.036	3349	390/415	550/610
500	0.022	0.030	0.022	0.036	0.377 + j0.28	0.031 + j0.035	3721	465/500	685/765
750	0.014	0.023	0.019	0.034	0.352 + j0.236	0.024 + j0.033	4288	565/610	885/990
1000	0.011	0.019	0.016	0.033	0.333 + j0.207	0.02 + j0.032	4758	640/690	1060/1185

* Ampacities are based on:

* For Duct: Table 310.60(C)(77) Detail 1.



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

- * For Free Air: Table 310.60(C)(69).
- * Inductive impedance is based on non-ferrous conduit with one diameter spacing.
- * Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
- * Capacitive Reactance is between Phase-to-Shield.

