

CU Compressed 15kV NLEPR Insulation 133% IL ARMOR-X[®] Red PVC Jacket. MV 105 Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Continuous Corrugated Welded Aluminum Armor - ARMOR-X[®], Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** ARMOR-X[®] Continuous Corrugated Welded Aluminum Armor
10. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV ARMOR-X[®] are armored cables for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, 250°C for short circuit conditions, and -50°C for cold bend. For uses in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Article 501, 502, and 503.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.003

- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- AIEC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

SOUTHWIRE ARMOR-X® {UL} MV-105 OR MC-HL 3/C SHIELDED XXX AWG CU 220 MILS NL-EPR 25%TS GW 1 X XXX AWG CU 90°C JKT DIR. BUR. FOR CT USE FT4 -40°C SUN. RES. 15KV 133% -- ABS CWC MC USA {YYYY} {NESC} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	inch	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch
890663	2	7	0.282	0.755	0.815	1x6	2.290	85	2.460	890	2674	1592	17.2
890664	1/0	19	0.361	0.840	0.900	1x4	2.550	75	2.700	1325	3357	2534	18.9
890665	2/0	19	0.405	0.884	0.944	1x4	2.550	75	2.700	1593	3639	3194	18.9
890666	4/0	19	0.512	0.976	1.036	1x3	2.750	75	2.900	2398	4769	5078	20.3
890667	250	37	0.558	1.028	1.088	1x2	2.880	75	3.030	2812	5332	6000	21.2
890668◇	350	37	0.661	1.127	1.187	1x2	3.220	85	3.390	3769	7406	8400	23.7
890669◇	500	37	0.789	1.252	1.312	1x1	3.540	85	3.710	5254	8900	12000	25.9
591219	500	37	0.789	1.275	1.335	1x4/0	3.540	85	3.710	5632	9177	12000	25.9
550439	750	58	0.968	1.404	1.464	1x1/0	3.850	85	4.020	7695	12407	18000	28.1

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.051	0.047	0.579 + j0.421	0.204 + j0.048	2571	150/160	165/185
1/0	0.102	0.128	0.043	0.043	0.5 + j0.385	0.128 + j0.043	2816	195/210	215/240
2/0	0.081	0.102	0.040	0.042	0.471 + j0.367	0.102 + j0.042	2952	220/235	245/275
4/0	0.051	0.065	0.034	0.039	0.426 + j0.328	0.065 + j0.039	3284	285/305	325/360
250	0.043	0.056	0.032	0.038	0.413 + j0.31	0.056 + j0.038	3451	310/335	360/400
350	0.031	0.041	0.028	0.036	0.388 + j0.28	0.041 + j0.036	3770	375/400	435/490
500	0.022	0.030	0.025	0.034	0.365 + j0.248	0.03 + j0.034	4167	450/485	535/600
500	0.022	0.030	0.025	0.034	0.365 + j0.248	0.03 + j0.034	4167	450/485	535/600
750	0.014	0.023	0.021	0.032	0.339 + j0.21	0.024 + j0.032	4752	545/585	670/745



- * Ampacities are based on:
 - * For Duct: Table 310.60(C)(79) Detail 1.
 - * For Free Air: Table 310.60(C)(71).
- * Inductive impedance is based on non-ferrous conduit with one diameter spacing.
- * Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
- * Capacitive Reactance is between Phase-to-Shield.

