

600V ST00W Cord with Jacket 105°C. Silicone Free

600 Volt, 105°C Flexible Cord. Heat and Moisture PVC Insulation and Sunlight, Heat, Moisture, Oil Resistant, and Flexible PVC Jacket. Rated for Extra Hard-Usage Service Cords. Approved for Outdoor use. Rated UL VW-1 and CSA FT1, FT2 Flame Resistant.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class K stranded bare copper per ASTM B3 and B174
- Insulation:** Heat, moisture, and oil resistant PVC (see Table 3 for insulation colors)
- Filler and Binder:** Fillers as needed to make core round and binder as needed to keep core assembly round on certain constructions (see Table 3 for details)
- Jacket:** Sunlight, heat, moisture, and oil resistant PVC (see Table 3 for jacket color)

APPLICATIONS AND FEATURES:

Southwire Type ST00W Flexible Cords are permitted for use as specified by Article 400 and related articles of the 2020 National Electric Code. Some typical applications for Type ST00W include, but are not limited to: Washing Machines and other large appliances, heavy-duty tools, motors and temporary electrical power and lighting installations for construction sites.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- RoHS-3 Complies with European Directive 2015/863

SAMPLE PRINT LEGEND:

(UL) VW-1 ST00W X/C XX AWG (X.XXmm²) 105(D)C DRY 60(D)C WATER RESISTANT 600V (CSA) FT1,FT2 LL90458

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
201940	16	12	65	30	100	0.69	279	5	See Table	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.





Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
201940	16	12	65	0.76	2.54	17.53	415	5	See Table	BK

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Table 3 - Filler, Binder, Insulation and Jacket Colors

Stock Number	Conductor Size	Conductor Number	Filler	Binder	Insulation Colors	Jacket Color
588011	16	3	None	White Tissue Paper	Black, White, Green	White
652927	16	3	None	White Tissue Paper	Black, White, Green-Yellow	Black
589056	16	3	None	White Tissue Paper	Black, White, Green-Yellow	Yellow
2074008	16	3	Polypropylene	None	Black, White, Red	Black
672344	16	3	Polypropylene	None	Black, White, Green	Black
560733	16	4	Paper	White Tissue Paper	Black, White, Green, Red	Yellow
587622	16	5	Polypropylene	White Tissue Paper	Black, White, Red, Orange, Green-Yellow	Yellow
588983	16	6	Polypropylene	White Tissue Paper	Black, White, Red, Green-Yellow, Orange, Blue	Yellow
578058	16	8	Polypropylene	White Tissue Paper	Black, White, Brown, Pink, Blue, Yellow, Orange, Red	Yellow
588986	16	8	PVC	White Tissue Paper	Black, White, Red, Green-Yellow, Orange, Blue, White-Black, Red-Black	Yellow
2019302	16	10	Polypropylene	Mylar	Black, White, Green-Yellow, Red, Orange-Black, Green-Black, Red-Black, White-Black, Blue, Orange	Yellow
2019402	16	12	Polypropylene	Mylar	Black, White, Red, Green-Yellow, Black-White, Blue-Black, Orange-Black, Green-Black, Red-Black, White-Black, Blue, Orange	Yellow
2632908	14	3	Polypropylene	None	Black, White, Green-Yellow	Black
672538	14	3	Polypropylene	None	Black, White, Green	Black
560703	14	3	None	White Tissue Paper	Black, White, Green	Yellow
593628	14	3	None	White Tissue Paper	Black, Green, Red	Yellow
578584	14	3	None	White Tissue Paper	Black, White, Green	Yellow
672540	12	3	Polypropylene	None	Black, White, Green	Black
560708	12	3	None	White Tissue Paper	Black, White, Green	Yellow
564743	12	4	Paper	White Tissue Paper	Black, White, Red, Green	Black
677522	10	3	Polypropylene	White Tissue Paper	Black, Red, Green	Black
6062109	10	4	Polypropylene	Mylar	Black, Black, Green-Yellow, Black	Gray

