



## Bare Copper Solid, Compressed Class B and C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Bare copper solid or compressed class B or C per ASTM B3 and ASTM B8

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors

**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Strand Class	Strand Count	Cond. Cmil	Diameter Over Conductor	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Rated Strength
	AWG/ kcmil		No. of Strands	cmil	inch	inch	lb/1000ft	Ω/1000ft	Ω/1000ft	lb
106955 <sup>◇</sup>	1/0	A	7	105600	0.367	0.368	326	0.102	0.122	844

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

