



## 300V Type SVT 105°C. Silicone-Free

300 Volt 105°C Vacuum Cleaner Cord. Not for Hard Usage. PVC Insulation and Jacket.



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Class M, Flexible Stranded Bare Copper per ASTM B-174
- Insulation:** Polyvinyl Chloride (PVC)
- Filler:** Polypropylene or Paper fillers as necessary for a round assembly
- Binder:** Tissue paper separator helically applied over the cabled conductors
- Jacket:** Polyvinyl Chloride (PVC) (Colors available upon request)

### APPLICATIONS AND FEATURES:

Southwire Type SVT Flexible Cords are permitted for use as specified by Article 400 and related articles of the National Electrical Code®. Some typical applications for Type SVT include, but are not limited to: vacuum cleaners, household food preparing machines, home entertainment appliances, blowers, etc.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- RoHS-3 Complies with European Directive 2015/863

### SAMPLE PRINT LEGEND:

(UL) VW-1 E46194 SVT X/C 18 AWG (0.824mm<sup>2</sup>) 105C 300V (CSA) FT1, FT2 LL90458

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
583974	18	2	41	15	30	0.240	32	10	BK,WE	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12

**Table 2 – Weights and Measurements (Metric)**

583974	18	2	41	0.38	0.76	6.10	48	10	BK,WE	BK
--------	----	---	----	------	------	------	----	----	-------	----

Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12





**Table 3 - Filler Type**

Stock Number	Filler
674048	No Filler
565289	No Filler
641182	No Filler
557988	Poly Filler
558107	Poly Filler
557989	Poly Filler
564616	Poly Filler
564753	Paper Filler
583974	Paper Filler
652970	Paper Filler
566072	Paper Filler
565073	Paper Filler
564650	Paper Filler
574829	Paper Filler

