



CU Compressed 5kV XLPE Insulation Airport Lighting

5000 Volt Non-Shielded Airport Lighting Cable, Copper Conductor With Cross-Linked Polyethylene Insulation XLPE. Meets (FAA) specification L-824 C For Underground Electrical Cable for Airport Lighting Circuits. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B stranded copper per ASTM B3 and B8
2. **Insulation:** Cross-Linked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Southwire's Airport Lighting Cable meets the requirements of (FAA) L-824 C underground electrical cable for airport lighting circuits (AC 150/5345-7F). Southwire's Airport Lighting Cable is available in sizes 8 AWG through 4 AWG 7 strands. The conductors are bare annealed copper class B and covered with an abrasion, moisture, and heat resistant Cross-Linked Polyethylene XLPE insulation. The 5kV non-shielded cable is available in black, red and yellow colors. Southwire Airport Lighting Cable is primarily used for series lighting circuits for runways, control systems, and other multi-purpose installations. It can be used in direct burial, conduit, or raceways. These cables are capable of operating continuously at a conductor temperature not in excess of 90°C for normal operation, 130°C for emergency and 250°C for short circuit conditions. Silicone Free.

- Cable is manufactured by Southwire Company in Douglas, GA USA
- Cable has a warranty of 1 year from date of installation or 2 years from date of shipment whichever comes first.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- FAA L-824 C Specification Approved by (AC 150/5345-7F)

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE X AWG 5000V XLPE 90°C FAA-L824, TYPE C





Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Cable Color
	AWG	No.	strands	inch	mil	inch	lb /1000ft	inch	
Airport Lighting									
643912	6	1	7	0.177	110	0.415	125	3.3	YW

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item



Ampacity

