



600V ROYAL® SOOW Cord Control with Black Jacket 90°C. MSHA Approved

600 Volt 90°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation, Heat, Moisture and Oil Resistant Flexible CPE Jacket



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Black CPE (Other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SOOW Flexible Cords UL/ CSA listed are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code. The cable is rated -40°C to 90°C, water, oil, and weather resistant. Southwire Type SOOW Flexible Cords are designed for extra hard usage on industrial equipment, heavy tools, battery chargers, portable lights, welding leads, marine dockside power, power extensions and mining applications.

SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- MSHA flame test - P07-KA070018-1MSHA
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- NEC Article 501.140 Class I Division 2
- Federal Specification J-C-580B

SAMPLE PRINT LEGEND:

SOUTHWIRE® ROYAL® CORD XX/C XX AWG ({mm²}) SOOW E46194 {UL} 600V -40°C TO 90°C -- {CSA} LL90458 SOOW 600V -40°C TO 90°C FT2 WATER RESISTANT {NOM}-ANCE -- {MSHA}

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.





Table 1 – Weights and Measurements

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
570042	832005	18	20	16	30	95	0.739	330	3	See Table	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Table 2 – Weights and Measurements (Metric)

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
		AWG/Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
570042	832005	18	20	16	0.76	2.41	18.77	491	3	See Table	BK

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.





Color Table

Stock Number	Size (AWG)	Conductor Number	Insulation Color	Filler/Binder
570034	18	10	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	None/Paper
570037	18	12	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Paper
598302	18	14	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	None/Paper
570039	18	16	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	None/Paper
570042	18	20	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	None/Paper
570043	18	24	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe	None/Paper
571692	18	30	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe, OE-WE 2xStripe, BE-WE 2xStripe, WE-BK 2xStripe, RD-BK 2xStripe, GN-BK 2xStripe, OE-BK 2xStripe	None/Paper
560526	16	10	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Paper
560527	16	12	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	Paper/Paper
598305	16	14	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Paper
560528	16	16	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	None/Paper
570018	16	20	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	None/Paper
570019	16	24	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe	None/Paper
570026	16	30	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe, OE-WE 2xStripe, BE-WE 2xStripe, WE-BK 2xStripe, RD-BK 2xStripe, GN-BK 2xStripe, OE-BK 2xStripe	Paper/Mylar
569994	14	10	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Paper
571270	14	12	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe	Paper/Paper
569995	14	14	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Paper
569997	14	16	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	Paper/String
571397	12	9	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe	None/Paper
569981	12	10	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Paper
569982	12	12	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Paper
598307	12	14	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Paper
569983	12	20	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	Poly/Paper





Stock Number	Size (AWG)	Conductor Number	Insulation Color	Filler/Binder
595662	10	10	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Paper
570006	10	12	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Paper

