



Thermocouple Wire PVC Insulation & Jacket

221°F 105°C Continuous



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Thermocouple wire per ANSI MC 96.1 & ASTM E230 (Solid or stranded available)
2. **Insulation:** Extruded PVC
3. **Overall Jacket:** Extruded PVC

APPLICATIONS AND FEATURES:

Widely used in all industry for extension grade applications and temperature sensors. Good flame retardance and chemical resistance. Good resistance to acids, moisture and abrasion. Excellent flexibility.

Stainless Steel, Inconel metal, or Tin Plated Copper overbraid is available on request. Type Ex, Jx, Kx, Tx and other Types available on request. Available with PLTC rating in single pair and multi pair constructions

SPECIFICATIONS:

- ASTM E230 Temperature-Electromotive Force (emf) Tables for Standardized Thermocouples
- ANSI MC 96.1 Temperature Measurement Thermocouples





Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Insul. Thickness mil	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
C4V_00	24	2	15	15	0.080 x 0.130	7	105	Type Ex, Jx, Kx, Tx
C4V_10	22	2	15	15	0.085 x 0.140	9	105	Type Ex, Jx, Kx, Tx
C4V_20	20	2	15	15	0.092 x 0.154	12	105	Type Ex, Jx, Kx, Tx
C4V_30	18	2	15	15	0.100 x 0.170	16	105	Type Ex, Jx, Kx, Tx
C4V_40	16	2	15	15	0.111 x 0.192	23	105	Type Ex, Jx, Kx, Tx
C4V_05	24(7)	2	15	15	0.084 x 0.138	8	105	Type Ex, Jx, Kx, Tx
C4V_25	20(7)	2	15	15	0.096 x 0.162	13	105	Type Ex, Jx, Kx, Tx
C4V_45	16(7)	2	15	15	0.118 x 0.206	24	105	Type Ex, Jx, Kx, Tx

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

0=Type Ex // 1=Type Jx // 2=Type Kx // 3=Type Tx

Conductor insulation and overall jacket are color coded per ANSI MC 96.1 and ASTM E230.

International color codes available on request.

Available in standard and special limits of error per ANSI MC 96.1, ASTM E230 and IEC 584.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Insul. Thickness mm	Jacket Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
C4V_00	24	2	0.38	0.38	2.03 x 3.30	10	105	Type Ex, Jx, Kx, Tx
C4V_10	22	2	0.38	0.38	2.16 x 3.56	13	105	Type Ex, Jx, Kx, Tx
C4V_20	20	2	0.38	0.38	2.34 x 3.91	18	105	Type Ex, Jx, Kx, Tx
C4V_30	18	2	0.38	0.38	2.54 x 4.32	24	105	Type Ex, Jx, Kx, Tx
C4V_40	16	2	0.38	0.38	2.82 x 4.88	34	105	Type Ex, Jx, Kx, Tx
C4V_05	24(7)	2	0.38	0.38	2.13 x 3.51	12	105	Type Ex, Jx, Kx, Tx
C4V_25	20(7)	2	0.38	0.38	2.44 x 4.11	19	105	Type Ex, Jx, Kx, Tx
C4V_45	16(7)	2	0.38	0.38	3.00 x 5.23	36	105	Type Ex, Jx, Kx, Tx

