



# NS75 CSA Triplex LLDPE/PVC Service Drop. ACSR Neutral - Messenger

Aluminum Conductors With Linear Low Density Polyethylene and Polyvinyl Chloride Insulation.




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Conductors are stranded, compact 1350-H19 aluminum
- Insulation:** Linear Low Density Polyethylene (LLDPE) and Polyvinyl Chloride (PVC)
- Messenger:** ACSR Neutral

## APPLICATIONS AND FEATURES:

Primarily used for 120 volt overhead service applications such as street lighting, outdoor lighting, and temporary service for construction. To be used at voltages of 600 volts phase-to-phase or less and at conductor temperatures not to exceed 90°C for linear low density polyethylene (LLDPE) and polyvinyl chloride (PVC) insulated conductors.

## SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ASTM B901 Standard Specification for Compressed Round Stranded Aluminum Conductors Using Single Input Wire Construction. *(The number of strands for both phase and neutral may differ)*
- ICEA S-76-474 Standard for Neutral-Supported Power Cable Assemblies with Weather-Resistant Extruded Insulation Rated 600V

**Table 1 – Weights and Measurements**

Stock Number	Phase Cond. Size	Phase Strand	Dia. Over Phase Conductor	Phase Insul. Thickness	Dia. Over Phase Insulation	Neutral Cond. Size	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	inch	mil	inch	AWG/Kcmil	inch	lb/1000ft
663253	6	7	0.169	75	0.319	6	0.689	143
663186	4	7	0.213	75	0.363	4	0.785	204
662267	2	7	0.268	75	0.418	2	0.903	298
662276	2/0	7	0.376	105	0.586	2/0	1.266	595

All dimensions are nominal and subject to normal manufacturing tolerances

1. The actual number of strands may differ for single input wire per ASTM B901





**Table 2 – Electrical and Engineering Data**

Phase Cond. Size AWG/Kcmil	Neutral Rated Breaking Strength lb	DC Resistance @ 25°C Ω/1000ft	AC Resistance @ 75°C Ω/1000ft	Inductive Reactance @ 60Hz Ω/1000ft	GMR ft
6	1190	0.6742	0.9237	0.0327	0.0054
4	1860	0.4239	0.5807	0.031	0.0068
2	2850	0.2666	0.3652	0.0296	0.0086
2/0	5310	0.1329	0.1821	0.0293	0.0122

Notes:

1. DC resistances include a 1% length factor for plexing.
2. Inductive reactance assumes the neutral is carrying current.
3. Phase conductors assumed to be reverse lay stranded, compressed construction.
4. Phase spacing assumes cables are touching.
5. Resistances shown are for the phase conductor only.
6. Ampacity based on conductor temperature of 90°; ambient temperature of 40°C; emissivity 0.9; 2 ft./sec. wind in sun.

**Neutral Code Word**

Size	Code Word	OD (inches)
#6	Bass	0.182
#4	Pike	0.229
#2	Carp	0.290
2/0	Hake	0.410

