



## Broadband Coax - RG59 Copper Braid Shield



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

#### Non-Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Copper braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

#### Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Foamed Fluoropolymer
3. **Shield:** Aluminum foil and braid shielded
4. **Jacket:** Low smoke Polyvinyl Chloride PVC. Polyethylene for outdoors

### APPLICATIONS AND FEATURES:

- CATV Applications for distributing television signals
- ALUMINUM BRAID CCTV Applications for surveillance
- Connecting security cameras, DVR or monitor using "BNC" connectors
- COPPER BRAID
- 75 Ohms Impedance

### SPECIFICATIONS:

- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® 92074 XX AWG RG59/U E57497 (UL) CL2 SUN RES

{SQFTG} SOUTHWIRE® SIGNAL® 99969 XX AWG RG59/U TYPE CL2P C(ETL)US CMP FT6

{SQFTG} SOUTHWIRE® SIGNAL® 99520 RG59 XX AWG BC 95% BRD TYPE CMR OR CL2R C(ETL)US 60°C SUN RES -- TYPE CMG FT4

{SQFTG} SOUTHWIRE® SIGNAL® RG59/U DIRECT BURIAL



**Table 1 – Physical and Electrical Data**

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type	Application
			AWG	No.		mil	mil	inch	lb /1000ft		
RG59											
92074	RG59	CM/CL2/ UL-1581	20	1	BC	55	30	0.234	28	Copper Braid	CATV, Sun Res
991057	RG59	CM/CL2/ UL-1581	22	1	CCS	55	35	0.242	33	Copper Braid	CATV, AWM 1354
991055	RG59	CM/CL2/ UL-1581	22	1	BC	55	30	0.242	36	Copper Braid	CATV, Sun Res
99969	RG59	CMP/CL2P/ UL-910	20	1	BC	55	30	0.196	26	Copper Braid	CATV, FT6
99520	RG59	CMR/CL2R/ UL-1666	22	1	BC	55	30	0.236	24	Copper Braid	CATV, CMG, FT4, Sun Res
192115	RG59	DIR BUR	20	1	BC	55	30	0.242	32	Copper Braid	CATV, Flooded

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◊ Cable marked with this symbol is a standard stock item