



HI-LO Supreme Parallel Water Well Cable Type THW

600V Extreme, Oil-Resistant, Moisture Resistant Conditions. Rated -50°C to +105°C,



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K, flexible stranded soft drawn bare copper per ASTM B172
2. **Insulation:** Polyvinyl Chloride (PVC) Type THW
3. **Jacket:** Thermoplastic elastomer (TPE)

APPLICATIONS AND FEATURES:

For use in residential, farm and industrial water well applications. Used in both Grounded and ungrounded water well cable systems. Conductors are parallel and insulated with PVC colored black, red, and yellow. Insulated and jacketed with a premium thermoplastic elastomer (TPE) material. Oil resistant. Used in both high temperature and low temperature wells

SPECIFICATIONS:

- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables

SAMPLE PRINT LEGEND:

SOUTHWIRE® E23919 XX AWG (X.XX{mm²}) {UL} 600V PUMP CABLE 90°C DRY 75°C WET {DD/MM/YYYY} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET





Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Cond. Strands No.	Diameter Over Conductor inch	Insul. Thickness mil	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
597855◇	14	3	41	0.073	30	25	0.188 X 0.464	65

All dimensions are nominal and subject to normal manufacturing tolerances
 ◇ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size AWG/ Kcmil	DC Resistance @ 25°C Ω/1000ft	AC Resistance @ 90°C Ω/1000ft	Inductive Reactance Ω/1000ft	Max Pull Tension lb	Min Bending Radius inch	Allowable Ampacity At 75°C Amp	Allowable Ampacity At 90°C Amp
14	2.814	3.391	0.058	98	1.9	20	25

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

