



## Bare Copper Solid, Compressed Class B and C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Bare copper solid or compressed class B or C per ASTM B3 and ASTM B8

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors

**Table 1 – Physical and Electrical Data**

| Stock Number        | Cond. Size | Strand Class | Strand Count   | Cond. Cmil | Cond. Number | Diameter Over Conductor | Approx. OD | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C | Rated Strength |
|---------------------|------------|--------------|----------------|------------|--------------|-------------------------|------------|----------------|----------------------|----------------------|----------------|
|                     | AWG/kcmil  |              | No. of Strands | cmil       | No.          | inch                    | inch       | lb/1000ft      | Ω/1000ft             | Ω/1000ft             | lb             |
| 106658 <sup>◇</sup> | 6          | B            | 7              | 26240      | 1            | 0.177                   | 0.177      | 81             | 0.411                | 0.495                | 209            |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

