

Thermocouple Wire EPR/CPE Multi Pair

Flexible Thermocouple Extension Cable, TC 600V 90°C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Thermocouple wire per ANSI MC 96.1 & ASTM E230 (Solid or stranded available)
- Insulation:** Extruded EPR
- Twisted Pair:** Conductors twisted together with a drain wire and alum/mylar shield
- Overall Shielded:** Aluminum / mylar shield and drain wire is applied over the core
- Overall Jacket:** Extruded CPE

APPLICATIONS AND FEATURES:

For use as a 600 volt, multi pair thermocouple cable where flame retardance, moisture/chemical resistance, and sunlight resistance are critical. Cable can be installed in free air, in raceways or direct burial. The cable is also approved for damp or dry locations as well as Class 1 Division II industrial hazardous locations per NEC 501-4(b) for (UL) Type Tray Cables (TC). Per ASTM E20 & ANSI MC 96.1. Positive conductor is numbered.

UL Type TC. Excellent physical properties and electrical properties. Resistance to flame, crush, compression and cuts. Good chemical resistance and mechanical strength. Flexible.

SPECIFICATIONS:

- ASTM E230 Temperature-Electromotive Force (emf) Tables for Standardized Thermocouples
- UL 1277 Vertical Cable Tray Flame Tests (70,000 BTU/Hr)
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202/FT4 Flame Test (70,000 BTU/hr) 350kcmil and Larger
- ANSI MC 96.1 Temperature Measurement Thermocouples

Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Insul. Thickness mil	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
C4E_20	20	31	45	0.270	39	90	Type TC

All dimensions are nominal and subject to normal manufacturing tolerances

∅ Cable marked with this symbol is a standard stock item

0=Type E // 1=Type J // 2=Type K // 3=Type T

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	mm	mm	mm	kg/km	°C	Style/Type
C4E_20	20	0.79	1.14	6.86	58	90	Type TC

