



CU 600V PVC-Nylon Insulation PVC Jacket THHN/THWN-2 Shielded. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type TC-ER, PLTC, FPL, and NFPL Control Cable 600 Volt Copper Conductors, Polyvinyl Chloride (PVC) with nylon layer Insulation THHN/THWN Polyvinyl Chloride (PVC) Jacket, Shielded Control Cable Conductor Identification Method 1 Table 2



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 7 strands class B compressed bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Polyvinyl Chloride (PVC) with nylon layer Type THHN/THWN
3. **Drain Wire:** Tinned copper
4. **Shielding:** 100% coverage aluminum foil
5. **Jacket:** Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's Type TC-ER, PLTC, FPL, and NFPL Control Cable are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C in dry locations and 75°C in wet locations, 105°C for emergency overload, and 150°C for short circuit conditions. For uses in Class I, II, and III per NEC Article 725 and 760. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10. Oil and sunlight resistant.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 13 Power-Limited Circuit Cables
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1277 TC-ER
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- EPA 40 CFR, Part 26, Subpart C heavy metals per Table 1, TCLP method

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® XX AWG (X.XX{mm²}) 4/C SHIELDED PVCN/PVC TYPE TC-ER THHN/THWN E75755 {UL} 600V 90°C DRY/75°C WET OIL RES I SUNLIGHT RESISTANT DIRECT BURIAL -- PLTC SUN RES --- FPL SUN RES --- NPLF SUN RES {NOM}-ANCE





Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C
	AWG	No.	strands	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp
14 AWG														
581276	14	2	7	15	45	0.323	33	66	2.631	3.170	0.058	1.3	20	25
TBA	14	3	7	20	45	0.334	51	111	2.631	3.170	0.058	1.3	20	25
TBA	14	4	7	20	45	0.362	64	128	2.631	3.170	0.058	1.4	16	20
TBA	14	5	7	20	45	0.393	76	148	2.631	3.170	0.058	1.6	16	20
TBA	14	7	7	20	45	0.426	102	186	2.631	3.170	0.058	1.7	14	17
TBA	14	9	7	20	45	0.493	128	230	2.631	3.170	0.058	2.0	14	17
TBA	14	12	7	20	60	0.584	166	303	2.631	3.170	0.058	2.3	10	12
TBA	14	19	7	20	60	0.676	256	433	2.631	3.170	0.058	2.7	10	12
TBA	14	24	7	20	60	0.786	320	535	2.631	3.170	0.058	3.1	9	11
12 AWG														
TBA	12	2	7	20	45	0.352	60	122	1.662	2.002	0.054	1.4	25	30
TBA	12	3	7	20	45	0.372	81	150	1.662	2.002	0.054	1.5	25	30
581600	12	4	7	15	45	0.422	93	148	1.662	2.002	0.054	1.7	20	24
TBA	12	5	7	20	45	0.442	121	204	1.662	2.002	0.054	1.8	20	24
TBA	12	7	7	20	45	0.480	162	260	1.662	2.002	0.054	1.9	17	21
581565	12	12	7	20	60	0.686	257	390	1.662	2.002	0.054	2.7	12	15
10 AWG														
TBA	10	2	7	25	45	0.422	96	178	1.040	1.253	0.050	1.7	35	40
TBA	10	3	7	25	45	0.448	129	220	1.040	1.253	0.050	1.8	35	40
646394	10	4	7	20	45	0.504	149	224	1.040	1.253	0.050	2.0	28	32
581567	10	5	7	20	45	0.588	182	288	1.040	1.253	0.050	2.4	28	32
TBA	10	7	7	25	60	0.615	258	407	1.040	1.253	0.050	2.5	24	28

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

