



600V CU EPR PAIRS CPE SPOS Instrumentation

Type TC-ER Instrumentation Cable 600 Volt Tinned Copper Conductors EPR Insulated Singles Shielded Pairs with Overall Shield SPOS. CPE Jacket Heat, Moisture, Oil and Sunlight Resistant. Rated for -30°C to 90°C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B stranded tinned copper per ASTM B3 and B33
2. **Insulation:** Flame-retardant Ethylene Propylene Rubber EPR Black/White alpha-numeric print alternate and inverted. 1-ONE, 2-TWO
3. **Drain Wire:** Tinned copper
4. **Twisted Shielded Pair:** 100% coverage aluminum/polyester foil shield with an individual drain wire shown in step 3
5. **Binder:** Mylar binder
6. **Overall Drain Wire:** Tinned Copper
7. **Overall Shielded:** 100% coverage aluminum/polyester foil shield with a drain wire as shown in step 6
8. **Rip Cord:** Rip cord under jacket for ease of removal
9. **Jacket:** Black sunlight, oil and moisture resistant thermoplastic Chlorinated Polyethylene CPE jacket

APPLICATIONS AND FEATURES:

Southwire's Instrumentation Cables Type TC-ER per UL 1277 are suitable for installations as outlined in NEC Article 336 for process control and instrumentation, control circuits for operation and interconnection of protective and signaling devices and for general use in manufacturing, industrial and commercial distribution systems. Cables are constructed with 7-strand tinned copper conductors insulated with Ethylene Propylene Rubber EPR. The paired conductors are colored black, white, and alpha-numeric printed. Each pair has an aluminum polyester foil with 100% coverage and a tinned drain wire. The overall assembly is covered with an aluminum polyester foil with 100% coverage and a tinned drain wire. The cable is suited for use in cable trays, raceways, conduit, aerial (when supported with a messenger) and direct burial. The cable is rated for -30°C to 90°C wet or dry and rated for Class I Div II hazardous locations, sun and oil resistant. The jacket is black Chlorinated Polyethylene CPE with a rip cord for easy removal

SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- EPA 40 CFR, Part 26, Subpart C heavy metals per Table 1, TCLP method





SAMPLE PRINT LEGEND:

SOUTHWIRE® XX AWG XX SHIELDED PAIRS EPR/CPE TYPE TC-ER E-FILE (UL) 600V 90°C WET/DRY SUN AND OIL RESI
DIRECT BURIAL-- FT4/IEEE 1202 SEQUENTIAL MARKING

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Number of Pairs	Diameter Over Conductor	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25°C
	AWG/ Kcmil	pair	inch	mil	mil	inch	lb/1000ft	inch	Ω/1000ft
630757	18	2	0.045	30	45	0.449	95	2.6	6.669
595480	18	4	0.045	30	60	0.658	175	3.9	6.669
TBA	18	8	0.045	30	60	0.767	253	4.6	6.669
TBA	18	12	0.045	30	80	0.922	385	5.5	6.669
TBA	18	24	0.045	30	80	1.257	688	7.5	6.669
TBA	18	36	0.045	30	80	1.558	986	9.3	6.669
592121	16	2	0.056	30	60	0.573	134	3.4	4.181
592123	16	4	0.056	30	60	0.697	252	4.1	4.181
592124	16	8	0.056	30	80	0.864	397	5.1	4.181
592120	16	12	0.056	30	80	1.014	561	6.0	4.181
592125	16	24	0.056	30	110	1.334	1077	8.0	4.181
TBA	16	36	0.056	30	110	1.758	1433	10.5	4.181

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Number of Pairs	Diameter Over Conductor	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25°C
	AWG/ Kcmil	pair	inch	mm	mm	mm	lb/km	mm	Ω/km
630757	18	2	0.045	0.76	1.14	11.40	141	66.04	21.88
595480	18	4	0.045	0.76	1.52	16.71	260	99.06	21.88
TBA	18	8	0.045	0.76	1.52	19.48	377	116.84	21.88
TBA	18	12	0.045	0.76	2.03	23.42	573	139.70	21.88
TBA	18	24	0.045	0.76	2.03	31.93	1024	190.50	21.88
TBA	18	36	0.045	0.76	2.03	39.57	1467	236.22	21.88
592121	16	2	0.056	0.76	1.52	14.55	199	86.36	13.72
592123	16	4	0.056	0.76	1.52	17.70	375	104.14	13.72
592124	16	8	0.056	0.76	2.03	21.95	591	129.54	13.72
592120	16	12	0.056	0.76	2.03	25.76	835	152.40	13.72
592125	16	24	0.056	0.76	2.79	33.88	1603	203.20	13.72
TBA	16	36	0.056	0.76	2.79	44.65	2133	266.70	13.72





Typical Electrical Specifications for Each Pair

Size	Capacitance	Inductance
18	40.66	0.0957
16	48.51	0.0895

