

## CU 2000V NLEPR/CPE RW90 Traction Cable

2000 Volt Single Conductor Copper, No Lead Ethylene Propylene Rubber(NL-EPR) insulation RW90 Chlorinated Polyethylene (CPE) Jacket



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Compressed stranded bare or tinned copper per ASTM B3 or B33 and B8. Center strand embossed with "Southwire, Year, Plant" when required
2. **Binder Tape:** Mylar Tape
3. **Insulation:** No Lead Ethylene Propylene Rubber (EPR) Type RW90
4. **Overall Jacket:** Thermoset Chlorinated Polyethylene (CPE) Jacket

### APPLICATIONS AND FEATURES:

Southwire 2000V EPR/CPE Cable is suited for use in mass transit and general industry applications where flexibility, fire resistance, and low smoke generation are a concern. May be installed in wet or dry locations in cable trays or raceways. These cables are capable of operating continuously at a conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload conditions, and 250°C for short circuit conditions. Resistance to moisture and most oils, acids, and alkalis with an overall durable thermoset CPE jacket. Alternate constructions available upon request.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- CSA C22.2 No.230 Tray Cables - Rated TC-ER
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- Oil Res I & Sun Res - AWG 8 & Larger
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)

### SAMPLE PRINT LEGEND:

{SQMTR} SOUTHWIRE® LL90458 {CSA} XXX KCMIL CU TYPE RW90 -40°C XX MILS EPR XX MILS CPE FT4 PR I PR II SUN RES OIL RES TC-ER 2000V YEAR OF MANUFACTURE



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

**Table 1 – Weights and Measurements**

Cond. Size	Strand	Insul. Thickness	Overall Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C†
AWG/Kcmil	No.	mil	mil	inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
1500	91	115	95	1.650	4977	8.2	12000	0.007	0.016	0.035	705

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

†Thicknesses reported as minimum average

\* Bare copper

**Table 2 – Weights and Measurements (Metric)**

Cond. Size	Strand	Insul. Thickness	Jacket Thickness <sup>1</sup>	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C
AWG/Kcmil	No.	mm	mm	mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp
1500	91	2.92	2.41	41.91	7407	208.28	53400	0.02	0.05	0.1148	705

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

†Thicknesses reported as minimum average

\* Bare copper

