

# FPLP - Fire Alarm Stranded Non-Shielded Plenum Rated LS-PVC

300V, 75°C, Multi-Conductor, Unshielded, Stranded Copper as FPLP.




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Stranded bare copper per ASTM B8
2. **Insulation:** Low Smoke Polyvinyl Chloride LS-PVC
3. **Rip Cord:** Rip cord for ease of jacket removal
4. **Jacket:** Low Smoke Polyvinyl Chloride LS-PVC, Color: RED

## APPLICATIONS AND FEATURES:

Fire protective signaling circuits. Also for smoke detectors, voice communications, audio control and initiating circuits. Article 760 of the NEC. For use in plenum spaces.

## SPECIFICATIONS:

- UL 1424 Cables for Power-Limited Fire-Alarm Circuits
- UL1424 Listed FPLR
- NFPA 70 NFPA 101, NFPA 130, and NFPA 502
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (90°C, 300V)
- RoHS-2 (European Directive 2011/65/EU)

## SAMPLE PRINT LEGEND:

XX AWG X/C E75610 c{UL}US CMP/CL3P/FPLP 75°C -- CMP FT6 MADE IN USA ROHS-2 COMPLIANT -- {MM/DD/YY}  
{HH:MM} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Rectance	Min Bending Radius	Allowable Ampacity At 60°C	Allowable Ampacity 75°C	Allowable Ampacity 90°C
	AWG	No.	strands	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp	Amp
14 AWG															
G60210-1	14	2	7	10	15	0.206	25	34	2.631	3.170	0.058	0.8	15	20	25

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item

Stock Number	Size AWG	Conductor Number	Black	Red
G40172-1	18	2	X	X
G50359-1	16	2	X	X
G60210-1	14	2	X	X

