

# CL3 Round Speaker Wire

300V, 75°C, CL3 Round Speaker Wire




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Bare copper Class K stranding per ASTM B172
2. **Insulation:** Polyvinyl Chloride PVC
3. **Rip Cord:** Rip cord for ease of jacket removal
4. **Jacket:** White Polyvinyl Chloride PVC.

## APPLICATIONS AND FEATURES:

Remote Control, Signalling, and Power-Limited circuits per NEC Article 725. 22AWG - 16 AWG also as communication circuits per NEC Article 800. Security, sound and audio, speaker cable, public address, intercom, sound reinforcement, alarm and access control circuits and power-limited controls.

- Flame Test: UL 1666
- Cable Type: CL3, Direct Burial Rating
- Voltage: 300 Volts
- Temperature: 75°C

## SPECIFICATIONS:

- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (90°C, 300V)

## SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® XX AWG X/C C(ETL)US TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES  
-- TYPE CMH FT1



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.003

Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Rectance
	AWG	No.	strands	inch	mil	inch	lb /1000ft	lb /1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft
16 AWG											
94564	16	4	65	0.059	20	0.228	32	44	4.487	5.406	0.033

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item

