

## 3/C CU 2000V EPDM/CPE Type G-GC Industrial Grade Cable 90°C. MSHA Approved

Flexible Copper conductors, Ethylene Propylene Diene Monomer (EPDM) insulation, Single Layer Chlorinated Polyethylene (CPE) Jacket



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Bare, soft drawn, annealed, flexible, rope-lay stranded copper per ASTM B3/B172
- Separator Tape:** Non-conducting tape applied between the conductor and insulation to facilitate stripping
- Insulation:** Ethylene Propylene Diene Monomer (EPDM). Color coded black, white, red
- Ground Check:** One insulated, bare, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B3/B172
- Ground Conductors:** Two insulated, bare, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B3/B172
- Fillers:** Paper fillers applied as needed to round the cable core
- Reinforcement Binder:** Reinforcing binder with twine applied over the core
- Jacket:** Black, flame resistant, thermosetting Chlorinated Polyethylene (CPE)

### APPLICATIONS AND FEATURES:

Southwire Type G-GC cable is a heavy-duty industrial cable for use in flexible, portable, and extra-hard usage applications where equipment grounding is required per NEC Article 400. Suitable for continuous submersion in water – ideal for submersible pumps, marine application. Also suitable for use in light to medium-duty mining applications. Sunlight and oil resistant. Highly flexible and easy to work with in cold conditions. Not for use as permanent building wiring. Meets FT-5 Flame Test. cUL Listed.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 1650 Standard for Portable Power Cable
- RoHS-2 (European Directive 2011/65/EU)

### SAMPLE PRINT LEGEND:

XXX AWG 3/C TYPE G-GC PORTABLE POWER CABLE 90°C - WET OR DRY 2000V OIL RESISTANT 60°C SUN RES. {UL}  
P-136-35-MSHA - AIW{TM} E172226 --- c{UL} FT1/FT5 (-40°C)



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Ground	Ground Check Size	Jacket Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	No.	inch	mil	No. x AWG	AWG	mil	inch	lb/1000ft
570098	1	3	224	0.300	80	2 x 6	1x8	145	1.455	1733

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity In Air 60°C	Allowable Ampacity In Air 75°C	Allowable Ampacity In Air 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	inch	Amp	Amp	Amp
1	0.137	0.164	0.046	7.2	131	156	177

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

