



**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Ampacity | Insul. Color | Jacket Color |
|--------------|------------|--------------|---------------|------------------|------------------|------------|----------------|----------|--------------|--------------|
|              | AWG/Kcmil  | No.          | No.           | mil              | mil              | inch       | lb/1000ft      | Amp      |              |              |
| 677043       | 16         | 2            | 65            | 30               | 45               | 0.315      | 56             | 13       | BK/WE        | Yellow       |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

\*\* Not a Federal and Military Specification JC-580B

\*\*\* Stock number: 677152 no paper fillers with Black jacket

**Table 2 – Weights and Measurements (Metric)**

| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Ampacity * | Insul. Color | Jacket Color |
|--------------|------------|--------------|---------------|------------------|------------------|------------|----------------|------------|--------------|--------------|
|              | AWG/Kcmil  | No.          | No.           | mm               | mm               | mm         | kg/km          | Amp        |              |              |
| 677043       | 16         | 2            | 65            | 0.76             | 1.14             | 8.00       | 83             | 13         | BK/WE        | Yellow       |

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

**Color Code**

| # of Conductor | Color Sequence           |
|----------------|--------------------------|
| 2              | Black, White             |
| 3              | Black, White, Green      |
| 4              | Black, White, Red, Green |

