

FEP 200°C 600V UL Type FEP

Flexible UL/CSA Approved Lead Wire, Temp Rating 200°C




Image not to scale. See Table 1 for dimensions.

- CONSTRUCTION:**
- 1. **Conductor:** Stranded tinned, annealed copper per ASTM B33
  - 2. **Insulation:** Extruded FEP fluoropolymer

**APPLICATIONS AND FEATURES:**

For use in accordance with the National Electric Code, Article 310. 200°C dry locations - special applications. 90°C dry and damp locations.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

- SPECIFICATIONS:**
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
  - UL AWM Appliance wire approvals as listed in Table 1
  - CSA AWM I A/B 600 FT1 FT2
  - RoHS-3 Complies with European Directive 2015/863

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Strands	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	strand	mil	inch	lb/1000ft	°C	Style/Type
C3126F	12	19/.0179	20	0.130	25	200	FEP

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item  
Dimensions and weights for other cable configurations are available upon request.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Strands	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	strand	mm	mm	kg/km	°C	Style/Type
C3126F	12	19/.0179	0.51	3.30	37	200	FEP