

HVTECK CU 1/C 140NLEPR TS PVC AIA PVC 8kV 133% CSA

Single Conductor, 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Inner Jacket:** PVC inner jacket
7. **Armour:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 8kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 kV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 kV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CU 140 NLEPR AIA 8kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/ Kcmil	No.	inch	inch	mil	inch	mil	inch	mil	inch	lb/1000ft	lb/1000ft
2	7	0.282	0.600	140	0.660	65	1.032	50	1.132	217	699
1	19	0.322	0.640	140	0.700	80	1.102	50	1.202	272	816
1/0	19	0.361	0.679	140	0.739	80	1.141	50	1.241	340	912
2/0	19	0.405	0.723	140	0.783	80	1.185	50	1.285	426	1029
3/0	19	0.456	0.774	140	0.834	80	1.346	50	1.446	535	1186
4/0	19	0.512	0.830	140	0.890	80	1.402	50	1.502	671	1364
250	37	0.558	0.884	140	0.944	80	1.456	50	1.556	790	1524
350	37	0.661	0.987	140	1.047	80	1.559	60	1.679	1102	1945
500	37	0.789	1.115	140	1.175	80	1.711	60	1.831	1568	2541
750	61	0.968	1.304	140	1.364	80	1.900	60	2.020	2343	3566
1000	61	1.117	1.453	140	1.513	110	2.109	60	2.229	3118	4587

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination



Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	13.6	530	0.162	0.204	0.035	0.054	0.564 + j0.486	0.205 + j0.055	2075	215	221
1	14.4	669	0.128	0.162	0.032	0.052	0.524 + j0.464	0.163 + j0.052	2199	245	247
1/0	14.9	844	0.102	0.128	0.030	0.050	0.491 + j0.445	0.129 + j0.050	2320	278	275
2/0	15.4	1064	0.081	0.102	0.027	0.048	0.466 + j0.424	0.103 + j0.048	2456	317	306
3/0	17.4	1342	0.064	0.081	0.025	0.048	0.443 + j0.401	0.082 + j0.048	2614	357	335
4/0	18.0	1692	0.051	0.065	0.023	0.046	0.426 + j0.379	0.066 + j0.047	2788	404	369
250	18.7	2000	0.043	0.056	0.021	0.045	0.415 + j0.358	0.057 + j0.045	2955	456	412
350	20.1	2800	0.031	0.041	0.019	0.043	0.394 + j0.323	0.042 + j0.043	3274	537	456
500	22.0	4000	0.022	0.030	0.016	0.041	0.373 + j0.285	0.031 + j0.041	3671	616	497
750	24.2	6000	0.014	0.023	0.014	0.039	0.349 + j0.239	0.024 + j0.039	4257	706	551
1000	26.7	8000	0.011	0.019	0.012	0.038	0.331 + j0.210	0.020 + j0.037	4718	813	596

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/Kcmil	No.	mm	mm	mm	mm	mm	mm	mm	mm	kg/km	kg/km
2	7	7.16	15.24	3.56	16.76	1.65	26.21	1.27	28.75	323	1040
1	19	8.18	16.26	3.56	17.78	2.03	27.99	1.27	30.53	405	1214
1/0	19	9.17	17.25	3.56	18.77	2.03	28.98	1.27	31.52	506	1357
2/0	19	10.29	18.36	3.56	19.89	2.03	30.10	1.27	32.64	634	1531
3/0	19	11.58	19.66	3.56	21.18	2.03	34.19	1.27	36.73	796	1765
4/0	19	13.00	21.08	3.56	22.61	2.03	35.61	1.27	38.15	999	2030
250	37	14.17	22.45	3.56	23.98	2.03	36.98	1.27	39.52	1176	2268
350	37	16.79	25.07	3.56	26.59	2.03	39.60	1.52	42.65	1640	2894
500	37	20.04	28.32	3.56	29.85	2.03	43.46	1.52	46.51	2333	3781
750	61	24.59	33.12	3.56	34.65	2.03	48.26	1.52	51.31	3487	5307
1000	61	28.37	36.91	3.56	38.43	2.79	53.57	1.52	56.62	4640	6826

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	345.44	2359	0.5315	0.67	0.0107	0.1772	0.564 + j0.486	0.205 + j0.055	2075	215	221
1	365.76	2977	0.4199	0.53	0.0098	0.1706	0.524 + j0.464	0.163 + j0.052	2199	245	247
1/0	378.46	3756	0.3346	0.42	0.0091	0.1640	0.491 + j0.445	0.129 + j0.050	2320	278	275
2/0	391.16	4735	0.2657	0.33	0.0082	0.1575	0.466 + j0.424	0.103 + j0.048	2456	317	306
3/0	441.96	5972	0.2100	0.27	0.0076	0.1575	0.443 + j0.401	0.082 + j0.048	2614	357	335
4/0	457.20	7529	0.1673	0.21	0.0070	0.1509	0.426 + j0.379	0.066 + j0.047	2788	404	369
250	474.98	8900	0.1411	0.18	0.0064	0.1476	0.415 + j0.358	0.057 + j0.045	2955	456	412
350	510.54	12460	0.1017	0.13	0.0058	0.1411	0.394 + j0.323	0.042 + j0.043	3274	537	456
500	558.80	17800	0.0722	0.10	0.0049	0.1345	0.373 + j0.285	0.031 + j0.041	3671	616	497
750	614.68	26700	0.0459	0.08	0.0043	0.1280	0.349 + j0.239	0.024 + j0.039	4257	706	551
1000	678.18	35600	0.0361	0.06	0.0037	0.1247	0.331 + j0.210	0.020 + j0.037	4718	813	596

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

