

HVTECK CU 1/C 220TRXLPE CB PVC AIA PVC 15kV 133% CSA

Single Conductor, 220 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Concentric Bond, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Shield:** Concentrically applied copper bond / shield wires. Complies with greater than the minimum requirement as per Table 44, CSA Standard C68.10 and Table 16A, Canadian Electrical Code Part 1
6. **Neutral Separator:** Mylar tape
7. **Inner Jacket:** PVC inner jacket
8. **Armour:** Aluminum Interlocked Armour (AIA)
9. **Overall Jacket:** Red Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 15kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CU 220 TRXLPE AIA 15kV 133% INS LEVEL CB [No. x SIZE] AWG SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil	No.	inch	inch	mil	inch	No. x AWG	mil	inch	mil	inch	lb/1000ft	lb/1000ft
TBA	2	7	0.282	0.760	220	0.820	7x14	80	1.440	50	1.540	299	1032
TBA	1	19	0.322	0.800	220	0.860	11x14	80	1.480	50	1.580	407	1175
TBA	1/0	19	0.361	0.839	220	0.899	11x14	80	1.519	60	1.639	474	1308
TBA	2/0	19	0.405	0.883	220	0.943	11x14	80	1.563	60	1.683	559	1432
TBA	3/0	19	0.456	0.934	220	0.994	13x14	80	1.614	60	1.734	694	1612
TBA	4/0	19	0.512	0.990	220	1.050	13x14	80	1.694	60	1.814	829	1829
TBA	250	37	0.558	1.044	220	1.104	17x14	80	1.748	60	1.868	1001	2055
TBA	350	37	0.661	1.147	220	1.207	21x14	80	1.885	60	2.005	1365	2620
672982	500	37	0.789	1.275	220	1.335	26x14	80	1.973	60	2.093	1863	3118
668996	750	61	0.968	1.464	220	1.524	21x12	110	2.222	75	2.342	2715	4258
TBA	750	61	0.968	1.464	220	1.524	21x12	110	2.262	75	2.412	2753	4523
672986	1000	61	1.117	1.613	220	1.673	21x12	110	2.369	75	2.519	3527	5277

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination



Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	18.5	530	0.162	0.204	0.062	0.061	0.563 + j0.421	0.205 + j0.062	5458	215	221
1	19.0	669	0.128	0.162	0.058	0.058	0.520 + j0.402	0.163 + j0.058	8577	245	247
1/0	19.7	844	0.102	0.128	0.053	0.056	0.485 + j0.386	0.129 + j0.057	8577	278	275
2/0	20.2	1064	0.081	0.102	0.049	0.054	0.458 + j0.368	0.103 + j0.055	8577	317	306
3/0	20.8	1342	0.064	0.081	0.046	0.052	0.435 + j0.349	0.082 + j0.053	10137	357	335
4/0	21.8	1692	0.051	0.065	0.042	0.051	0.415 + j0.330	0.066 + j0.051	10137	404	369
250	22.4	2000	0.043	0.056	0.039	0.049	0.403 + j0.313	0.057 + j0.050	13256	456	412
350	24.1	2800	0.031	0.041	0.035	0.047	0.379 + j0.284	0.042 + j0.047	16376	537	456
500	25.1	4000	0.022	0.030	0.030	0.044	0.358 + j0.252	0.031 + j0.044	20275	616	497
750	28.1	6000	0.014	0.023	0.026	0.042	0.333 + j0.214	0.024 + j0.042	26018	706	551
750	28.9	6000	0.014	0.023	0.026	0.043	0.333 + j0.214	0.024 + j0.043	26018	706	551
1000	30.2	8000	0.011	0.019	0.023	0.040	0.315 + j0.189	0.020 + j0.040	26018	813	596

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil	No.	mm	mm	mm	mm	No. x AWG	mm	mm	mm	mm	kg/km	kg/km
TBA	2	7	7.16	19.30	5.59	20.83	7x14	2.03	36.58	1.27	39.12	445	1536
TBA	1	19	8.18	20.32	5.59	21.84	11x14	2.03	37.59	1.27	40.13	606	1749
TBA	1/0	19	9.17	21.31	5.59	22.83	11x14	2.03	38.58	1.52	41.63	705	1947
TBA	2/0	19	10.29	22.43	5.59	23.95	11x14	2.03	39.70	1.52	42.75	832	2131
TBA	3/0	19	11.58	23.72	5.59	25.25	13x14	2.03	41.00	1.52	44.04	1033	2399
TBA	4/0	19	13.00	25.15	5.59	26.67	13x14	2.03	43.03	1.52	46.08	1234	2722
TBA	250	37	14.17	26.52	5.59	28.04	17x14	2.03	44.40	1.52	47.45	1490	3058
TBA	350	37	16.79	29.13	5.59	30.66	21x14	2.03	47.88	1.52	50.93	2031	3899
672982	500	37	20.04	32.39	5.59	33.91	26x14	2.03	50.11	1.52	53.16	2772	4640
668996	750	61	24.59	37.19	5.59	38.71	21x12	2.79	56.44	1.91	59.49	4040	6337
TBA	750	61	24.59	37.19	5.59	38.71	21x12	2.79	57.45	1.91	61.26	4097	6731
672986	1000	61	28.37	40.97	5.59	42.49	21x12	2.79	60.17	1.91	63.98	5249	7853

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	469.90	2359	0.5315	0.67	0.0189	0.2001	0.563 + j0.421	0.205 + j0.062	5458	215	221
1	482.60	2977	0.4199	0.53	0.0177	0.1903	0.520 + j0.402	0.163 + j0.058	8577	245	247
1/0	500.38	3756	0.3346	0.42	0.0162	0.1837	0.485 + j0.386	0.129 + j0.057	8577	278	275
2/0	513.08	4735	0.2657	0.33	0.0149	0.1772	0.458 + j0.368	0.103 + j0.055	8577	317	306
3/0	528.32	5972	0.2100	0.27	0.0140	0.1706	0.435 + j0.349	0.082 + j0.053	10137	357	335
4/0	553.72	7529	0.1673	0.21	0.0128	0.1673	0.415 + j0.330	0.066 + j0.051	10137	404	369
250	568.96	8900	0.1411	0.18	0.0119	0.1608	0.403 + j0.313	0.057 + j0.050	13256	456	412
350	612.14	12460	0.1017	0.13	0.0107	0.1542	0.379 + j0.284	0.042 + j0.047	16376	537	456
500	637.54	17800	0.0722	0.10	0.0091	0.1444	0.358 + j0.252	0.031 + j0.044	20275	616	497
750	713.74	26700	0.0459	0.08	0.0079	0.1378	0.333 + j0.214	0.024 + j0.042	26018	706	551
750	734.06	26700	0.0459	0.08	0.0079	0.1411	0.333 + j0.214	0.024 + j0.043	26018	706	551
1000	767.08	35600	0.0361	0.06	0.0070	0.1312	0.315 + j0.189	0.020 + j0.040	26018	813	596

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

