

MC-AP™ Type MC All Purpose THHN/THWN Circuit Size Copper Conductor 120/208V Colors

Copper THHN Insulated Conductors. Full-Sized Aluminum Equipment Grounding/Bonding Conductor. UL Listed 600 Volt. Rated VW1. Lightweight Aluminum Interlocked Armor is Part of Equipment Bonding/Grounding Path.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or 19 strands class C compressed copper per ASTM B3 and ASTM B8
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Binder:** Mylar tape
4. **Ground:** Full-sized bare 8000 series aluminum grounding/bonding conductor. Armor and bare aluminum conductor form the equipment ground path.
5. **Armor:** Aluminum Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire MC-AP All Purpose Type MC Cable is suitable for use as follows:

- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi- residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire Armorlite® Type MC Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Jan. 31, 2024, 12:31 a.m. UTC REVISION: 1.000.005

- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- RoHS-2 (European Directive 2011/65/EU)
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS -- ARMOR IS EQUIPMENT GROUNDING PATH COMPONENT

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/Kcmil			inch		mils	inch	lbs/1000ft	lbs/1000ft
555272◇	14	2	BK/WE	0.064	Solid	20	0.451	25	70
555273◇	14	3	BK/RD/WE	0.064	Solid	20	0.468	37	87
555274◇	14	4	BK/RD/BE/WE	0.064	Solid	20	0.495	50	105
555103◇	12	2	BK/WE	0.080	Solid	20	0.487	39	92
558768◇	12	2	RD/WE	0.080	Solid	20	0.493	39	92
558770◇	12	2	BE/WE	0.080	Solid	20	0.487	39	92
555104◇	12	3	BK/RD/WE	0.080	Solid	20	0.506	59	117
555105◇	12	4	BK/RD/BE/WE	0.080	Solid	20	0.544	79	145
555275◇	10	2	BK/WE	0.101	Solid	25	0.555	61	130
555277◇	10	3	BK/RD/WE	0.101	Solid	25	0.580	92	169
555278◇	10	4	BK/RD/BE/WE	0.101	Solid	25	0.619	123	210
556377◇	12	2	BK/WE	0.090	19	20	0.438	40	90
558786◇	12	2	RD/WE	0.090	19	20	0.507	40	95
558788◇	12	2	BE/WE	0.090	19	20	0.507	40	95
556457◇	12	3	BK/RD/WE	0.090	19	20	0.528	60	122
555874◇	12	4	BK/RD/BE/WE	0.090	19	20	0.562	80	150
557387◇	10	2	BK/WE	0.117	19	25	0.586	64	139
557390◇	10	3	BK/RD/WE	0.117	19	25	0.613	97	181

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item



Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 60°C	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
14	2	3.2	2.631	3.170	0.058	15	20	25
14	3	3.3	2.631	3.170	0.058	15	20	25
14	4	3.5	2.631	3.170	0.058	12	16	20
12	2	3.4	1.662	2.002	0.054	20	25	30
12	2	3.5	1.662	2.002	0.054	20	25	30
12	2	3.4	1.662	2.002	0.054	20	25	30
12	3	3.5	1.662	2.002	0.054	20	25	30
12	4	3.8	1.662	2.002	0.054	16	20	24
10	2	3.9	1.040	1.253	0.050	30	35	40
10	3	4.1	1.040	1.253	0.050	30	35	40
10	4	4.3	1.040	1.253	0.050	24	28	32
12	2	3.1	1.662	2.002	0.054	20	25	30
12	2	3.5	1.662	2.002	0.054	20	25	30
12	2	3.5	1.662	2.002	0.054	20	25	30
12	3	3.7	1.662	2.002	0.054	20	25	30
12	4	3.9	1.662	2.002	0.054	16	20	24
10	2	4.1	1.040	1.253	0.050	30	35	40
10	3	4.3	1.040	1.253	0.050	30	35	40

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

