

35kV AL 100% TRXLPE One-Sixth Neutral (Based on Short Circuit) HI-DRI-PLUS® Renewable (Solar or Wind)

Moisture Blocked Aluminum Conductors. TRXLP Insulation. One-Sixth Copper Concentric Neutrals. XLPE Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture Blocked 1350 H16/H26 Aluminum, Class B Compressed or Compressed Unilay Stranded
2. **Strand Shield:** Semi-conducting Crosslinked Polyethylene
3. **Insulation:** Tree Retardant Crosslinked Polyethylene (TRXLPE)
4. **Insulation Shield:** Strippable Semi-conducting Crosslinked Polyethylene
5. **Concentric Neutral:** Annealed Copper Wires Helically Applied One-Sixth Concentric Neutral
6. **Overall Jacket & Water Block:** HI-DRI-PLUS® Water Swellable Powder Black Crosslinked Polyethylene (XLPE) with Red Extruded Stripes

APPLICATIONS AND FEATURES:

- Predominately used for renewable projects with wind or solar applications.
- Suitable for use in wet or dry locations, direct burial, underground ducts, and exposure to direct sunlight.
- To be used at conductor temperature not to exceed 105°C normal operation.
- UL listed MV-105
- The concentric neutral counts and sizes listed in Table 1 are based on the ICEA P-45-482 short circuit calculation of an MV-90 design. The short circuit value in Table 1 is calculated using a higher thermal limit of a crosslinked XLPE jacket MV-105 design.

SPECIFICATIONS:

- UL 1072 Medium-Voltage Power Cables
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE(R) HI-DRI-PLUS(R) (UL) XXX KCMIL AL 345 MILS TRXLPE TYPE MV-105 35KV 100% INSUL LEVEL -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Jan. 18, 2024, 9:59 p.m. UTC REVISION: 1.000.014

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
662806	350 (37)	0.641	1.391	345	1.501	7x14	0.375	75	1.783	1328	14.3	2100
626336	750 (61)	0.938	1.708	345	1.848	14x14	0.187	75	2.130	2106	17.0	4500
622377	750 (61)	0.968	1.708	345	1.848	14x14	0.187	75	2.130	2105	17.0	4500
626346	1000 (61)	1.084	1.857	345	1.997	12x12	0.138	75	2.312	2588	18.5	6000
620742	1000 (61)	1.117	1.857	345	1.997	19x14	0.138	75	2.279	2533	18.2	6000
623076	1000 (61)	1.117	1.857	345	1.997	18x14	0.146	75	2.279	2521	18.2	6000
618443	1000 (61)	1.117	1.857	345	1.997	25x14	0.105	75	2.279	2610	18.2	6000
662112	1250 (91)	1.212	2.000	345	2.140	23x14	0.114	75	2.422	2942	19.4	7500
626351	1250 (91)	1.212	2.000	345	2.140	15x12	0.110	75	2.455	2997	19.6	7500
622362	1250 (91)	1.250	2.000	345	2.140	15x12	0.110	75	2.455	2996	19.6	7500

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item



Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
350 (37)	0.050	0.065	0.049	0.045	0.41	2.47	0.119 + j0.724	0.065 + j0.044	3621	315	375
750 (61)	0.024	0.033	0.037	0.040	0.54	3.24	0.087 + j0.707	0.033 + j0.040	7242	480	550
750 (61)	0.024	0.033	0.036	0.040	0.55	3.33	0.087 + j0.706	0.033 + j0.04	7242	480	550
1000 (61)	0.018	0.026	0.033	0.039	0.60	3.61	0.080 + j0.700	0.026 + j0.038	9862	550	615
1000 (61)	0.018	0.026	0.032	0.038	0.61	3.72	0.080 + j0.700	0.026 + j0.038	9828	550	615
1000 (61)	0.018	0.026	0.033	0.038	0.61	3.69	0.080 + j0.700	0.026 + j0.038	9311	550	615
1000 (61)	0.018	0.026	0.034	0.038	0.34	6.76	0.080 + j0.700	0.026 + j0.038	12932	550	615
1250 (91)	0.014	0.023	0.031	0.037	0.65	3.93	0.077 + j0.439	0.023 - j0.220	11898		
1250 (91)	0.014	0.023	0.031	0.038	0.65	3.93	0.077 + j0.438	0.023 - j0.219	12328		
1250 (91)	0.014	0.023	0.030	0.037	0.67	4.03	0.077 + j0.693	0.023 + j0.037	12328		

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
662806	350 (37)	16.28	35.33	8.76	38.13	7x14	1.23	1.91	45.29	1976	363.22	9345
626336	750 (61)	23.83	43.38	8.76	46.94	14x14	0.61	1.91	54.10	3134	431.80	20025
622377	750 (61)	24.59	43.38	8.76	46.94	14x14	0.61	1.91	54.10	3133	431.80	20025
626346	1000 (61)	27.53	47.17	8.76	50.72	12x12	0.45	1.91	58.72	3851	469.90	26700
620742	1000 (61)	28.37	47.17	8.76	50.72	19x14	0.45	1.91	57.89	3770	462.28	26700
623076	1000 (61)	28.37	47.17	8.76	50.72	18x14	0.48	1.91	57.89	3752	462.28	26700
618443	1000 (61)	28.37	47.17	8.76	50.72	25x14	0.34	1.91	57.89	3884	462.28	26700
662112	1250 (91)	30.78	50.80	8.76	54.36	23x14	0.37	1.91	61.52	4378	492.76	33375
626351	1250 (91)	30.78	50.80	8.76	54.36	15x12	0.36	1.91	62.36	4460	497.84	33375
622362	1250 (91)	31.75	50.80	8.76	54.36	15x12	0.36	1.91	62.36	4459	497.84	33375

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
350 (37)	0.1640	0.21	0.0149	0.1476	1.345	8.1037	0.119 + j0.724	0.065 + j0.044	3621	315	375
750 (61)	0.0787	0.11	0.0113	0.1312	1.772	10.6299	0.087 + j0.707	0.033 + j0.040	7242	480	550
750 (61)	0.0787	0.11	0.0110	0.1312	1.804	10.9252	0.087 + j0.706	0.033 + j0.04	7242	480	550
1000 (61)	0.0591	0.09	0.0101	0.1280	1.969	11.8438	0.080 + j0.700	0.026 + j0.038	9862	550	615
1000 (61)	0.0591	0.09	0.0098	0.1247	2.001	12.2047	0.080 + j0.700	0.026 + j0.038	9828	550	615
1000 (61)	0.0591	0.09	0.0101	0.1247	2.001	12.1063	0.080 + j0.700	0.026 + j0.038	9311	550	615
1000 (61)	0.0591	0.09	0.0104	0.1247	1.115	22.1785	0.080 + j0.700	0.026 + j0.038	12932	550	615
1250 (91)	0.0459	0.08	0.0094	0.1214	2.133	12.8937	0.077 + j0.439	0.023 - j0.220	11898		
1250 (91)	0.0459	0.08	0.0094	0.1247	2.133	12.8937	0.077 + j0.438	0.023 - j0.219	12328		
1250 (91)	0.0459	0.08	0.0091	0.1214	2.198	13.2218	0.077 + j0.693	0.023 + j0.037	12328		

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator

