

15kV AL 133% TRXLPE Full Neutral LLDPE Patented POWERGLIDE® MV CABLE (PATENT: www.patentsw.com)

Single Conductor, 220 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed Aluminum ASTM B231 1350 ¾ hard H16/H26 (Non Moisture Blocked Optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 220 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket with PowerGlide® Technology. Black with red extruded stripes

For information about our Cable-Rejuvenation Services please visit us at: [Cable-Rejuvenation Services](#)

You can email us at: [Cable-Rejuvenation Services](#)

APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation. 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B609 Standard Specification for Aluminum 1350 Round Wire, Annealed and Intermediate Tempers, for Electrical Purposes
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AIEC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:37 p.m. UTC REVISION: 1.000.001

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] AL 15000 VOLTS TRXLPE INSULATION 220 MILS -- (NESC) --
 SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	2 (Solid)	0.257	0.735	220	0.825	10x14	0.263	50	1.053	544	8.4	398
TBA	2 (7)	0.282	0.760	220	0.850	10x14	0.263	50	1.078	556	8.6	398
TBA	1 (Solid)	0.289	0.767	220	0.857	13x14	0.202	50	1.085	617	8.7	502
TBA	1 (19)	0.322	0.800	220	0.890	13x14	0.202	50	1.118	635	8.9	502
TBA	1/0 (Solid)	0.324	0.802	220	0.892	16x14	0.164	50	1.120	698	9.0	633
TBA	1/0 (19)	0.351	0.829	220	0.919	16x14	0.164	50	1.147	714	9.2	633
TBA	2/0 (19)	0.395	0.873	220	0.963	20x14	0.131	50	1.191	817	9.5	798
TBA	3/0 (19)	0.443	0.921	220	1.011	25x14	0.105	50	1.239	943	9.9	1006
TBA	4/0 (19)	0.498	0.976	220	1.066	32x14	0.082	50	1.294	1109	10.4	1269
TBA	250 (37)	0.558	1.044	220	1.154	25x12	0.066	50	1.416	1297	11.3	1500
TBA	350 (37)	0.661	1.147	220	1.257	32x12	0.051	50	1.519	1595	12.2	2100

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.162	0.204	0.071	0.054	0.070	0.61	0.258 + j0.768	0.204 + j0.053	3487	120	150
2 (7)	0.266	0.336	0.067	0.052	0.074	0.64	0.390 + j0.767	0.336 + j0.054	3487	120	150
1 (Solid)	0.129	0.162	0.066	0.052	0.075	0.65	0.216 + j0.763	0.162 + j0.050	4533	140	170
1 (19)	0.211	0.266	0.061	0.050	0.080	0.69	0.320 + j0.761	0.266 + j0.051	4533	140	170
1/0 (Solid)	0.102	0.128	0.061	0.050	0.081	0.70	0.182 + j0.759	0.128 + j0.048	5579	155	195
1/0 (19)	0.167	0.211	0.058	0.049	0.085	0.74	0.265 + j0.757	0.211 + j0.049	5579	155	195
2/0 (19)	0.133	0.167	0.053	0.047	0.092	0.80	0.221 + j0.753	0.167 + j0.047	6974	180	220
3/0 (19)	0.105	0.132	0.049	0.045	0.100	0.87	0.186 + j0.749	0.132 + j0.045	8718	205	250
4/0 (19)	0.084	0.105	0.045	0.044	0.109	0.94	0.159 + j0.744	0.105 + j0.043	11159	235	285
250 (37)	0.071	0.090	0.042	0.043	0.117	1.01	0.144 + j0.738	0.090 + j0.043	13852	254	307
350 (37)	0.050	0.065	0.037	0.041	0.133	1.15	0.119 + j0.731	0.065 + j0.041	17730	305	365

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	2 (Solid)	6.53	18.67	5.59	20.96	10x14	0.86	1.27	26.75	810	213.36	1771
TBA	2 (7)	7.16	19.30	5.59	21.59	10x14	0.86	1.27	27.38	827	218.44	1771
TBA	1 (Solid)	7.34	19.48	5.59	21.77	13x14	0.66	1.27	27.56	918	220.98	2234
TBA	1 (19)	8.18	20.32	5.59	22.61	13x14	0.66	1.27	28.40	945	226.06	2234
TBA	1/0 (Solid)	8.23	20.37	5.59	22.66	16x14	0.54	1.27	28.45	1039	228.60	2817
TBA	1/0 (19)	8.92	21.06	5.59	23.34	16x14	0.54	1.27	29.13	1063	233.68	2817
TBA	2/0 (19)	10.03	22.17	5.59	24.46	20x14	0.43	1.27	30.25	1216	241.30	3551
TBA	3/0 (19)	11.25	23.39	5.59	25.68	25x14	0.34	1.27	31.47	1403	251.46	4477
TBA	4/0 (19)	12.65	24.79	5.59	27.08	32x14	0.27	1.27	32.87	1650	264.16	5647
TBA	250 (37)	14.17	26.52	5.59	29.31	25x12	0.22	1.27	35.97	1930	287.02	6675
TBA	350 (37)	16.79	29.13	5.59	31.93	32x12	0.17	1.27	38.58	2374	309.88	9345

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.5315	0.67	0.0216	0.1772	0.230	2.0013	0.258 + j0.768	0.204 + j0.053	3487	120	150
2 (7)	0.8727	1.10	0.0204	0.1706	0.243	2.0997	0.390 + j0.767	0.336 + j0.054	3487	120	150
1 (Solid)	0.4232	0.53	0.0201	0.1706	0.246	2.1325	0.216 + j0.763	0.162 + j0.050	4533	140	170
1 (19)	0.6923	0.87	0.0186	0.1640	0.262	2.2638	0.320 + j0.761	0.266 + j0.051	4533	140	170
1/0 (Solid)	0.3346	0.42	0.0186	0.1640	0.266	2.2966	0.182 + j0.759	0.128 + j0.048	5579	155	195
1/0 (19)	0.5479	0.69	0.0177	0.1608	0.279	2.4278	0.265 + j0.757	0.211 + j0.049	5579	155	195
2/0 (19)	0.4364	0.55	0.0162	0.1542	0.302	2.6247	0.221 + j0.753	0.167 + j0.047	6974	180	220
3/0 (19)	0.3445	0.43	0.0149	0.1476	0.328	2.8543	0.186 + j0.749	0.132 + j0.045	8718	205	250
4/0 (19)	0.2756	0.34	0.0137	0.1444	0.358	3.0840	0.159 + j0.744	0.105 + j0.043	11159	235	285
250 (37)	0.2329	0.30	0.0128	0.1411	0.384	3.3136	0.144 + j0.738	0.090 + j0.043	13852	254	307
350 (37)	0.1640	0.21	0.0113	0.1345	0.436	3.7730	0.119 + j0.731	0.065 + j0.041	17730	305	365

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator

