

25kV CU 100% TRXLPE Full Neutral LLDPE

Single Conductor, 260 Mils Tree Retardant Cross Linked Polyethylene, 100% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 260 Mils Tree Retardant Cross Linked Polyethylene 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 25kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation. 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 25000 VOLTS TRXLPE INSULATION 260 MILS -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:37 p.m. UTC REVISION: 1.000.000

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	1 (Solid)	0.289	0.847	260	0.937	20x14	0.131	50	1.165	960	9.3	669
621618	1 (19)	0.322	0.872	260	0.962	20x14	0.131	50	1.190	932	9.5	669
TBA	1/0 (Solid)	0.324	0.882	260	0.972	25x14	0.105	50	1.200	1116	9.6	844
628269	1/0 (19)	0.361	0.912	260	1.002	16x12	0.103	50	1.263	1114	10.1	844
TBA	2/0 (19)	0.405	0.963	260	1.053	32x14	0.082	50	1.281	1348	10.2	1064
628272	2/0 (19)	0.405	0.956	260	1.046	13x10	0.080	50	1.349	1351	10.8	1064
TBA	3/0 (19)	0.456	1.014	260	1.124	25x12	0.066	50	1.386	1598	11.1	1342
628274	4/0 (19)	0.512	1.062	260	1.172	20x10	0.052	50	1.475	1897	11.8	1692
TBA	250 (37)	0.558	1.124	260	1.234	25x10	0.041	50	1.538	2241	12.3	2000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.128	0.162	0.073	0.054	0.114	1.65	0.216 + j0.759	0.162 + j0.052	6974	175	220
1 (19)	0.128	0.162	0.068	0.052	0.121	1.75	0.216 + j0.758	0.162 + j0.052	6974	175	220
1/0 (Solid)	0.102	0.128	0.067	0.052	0.122	1.76	0.182 + j0.755	0.128 + j0.050	8718	200	250
1/0 (19)	0.102	0.128	0.063	0.051	0.131	1.89	0.182 + j0.753	0.128 + j0.051	8865	200	250
2/0 (19)	0.081	0.102	0.058	0.048	0.141	2.04	0.156 + j0.750	0.102 + j0.048	11159	225	280
2/0 (19)	0.081	0.102	0.058	0.049	0.141	2.04	0.156 + j0.747	0.102 + j0.050	11450	225	280
3/0 (19)	0.064	0.081	0.054	0.047	0.153	2.21	0.135 + j0.743	0.081 + j0.048	13852	260	315
4/0 (19)	0.051	0.065	0.050	0.046	0.166	2.40	0.119 + j0.738	0.065 + j0.046	17615	295	355
250 (37)	0.043	0.056	0.047	0.045	0.175	2.53	0.111 + j0.734	0.056 + j0.045	22019	318	360

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	1 (Solid)	7.34	21.51	6.60	23.80	20x14	0.43	1.27	29.59	1429	236.22	2977
621618	1 (19)	8.18	22.15	6.60	24.43	20x14	0.43	1.27	30.23	1387	241.30	2977
TBA	1/0 (Solid)	8.23	22.40	6.60	24.69	25x14	0.34	1.27	30.48	1661	243.84	3756
628269	1/0 (19)	9.17	23.16	6.60	25.45	16x12	0.34	1.27	32.08	1658	256.54	3756
TBA	2/0 (19)	10.29	24.46	6.60	26.75	32x14	0.27	1.27	32.54	2006	259.08	4735
628272	2/0 (19)	10.29	24.28	6.60	26.57	13x10	0.26	1.27	34.26	2011	274.32	4735
TBA	3/0 (19)	11.58	25.76	6.60	28.55	25x12	0.22	1.27	35.20	2378	281.94	5972
628274	4/0 (19)	13.00	26.97	6.60	29.77	20x10	0.17	1.27	37.47	2823	299.72	7529
TBA	250 (37)	14.17	28.55	6.60	31.34	25x10	0.13	1.27	39.07	3335	312.42	8900



All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.4199	0.53	0.0223	0.1772	0.374	5.4134	0.216 + j0.759	0.162 + j0.052	6974	175	220
1 (19)	0.4199	0.53	0.0207	0.1706	0.397	5.7415	0.216 + j0.758	0.162 + j0.052	6974	175	220
1/0 (Solid)	0.3346	0.42	0.0204	0.1706	0.400	5.7743	0.182 + j0.755	0.128 + j0.050	8718	200	250
1/0 (19)	0.3346	0.42	0.0192	0.1673	0.430	6.2008	0.182 + j0.753	0.128 + j0.051	8865	200	250
2/0 (19)	0.2657	0.33	0.0177	0.1575	0.463	6.6929	0.156 + j0.750	0.102 + j0.048	11159	225	280
2/0 (19)	0.2657	0.33	0.0177	0.1608	0.463	6.6929	0.156 + j0.747	0.102 + j0.050	11450	225	280
3/0 (19)	0.2100	0.27	0.0165	0.1542	0.502	7.2507	0.135 + j0.743	0.081 + j0.048	13852	260	315
4/0 (19)	0.1673	0.21	0.0152	0.1509	0.545	7.8740	0.119 + j0.738	0.065 + j0.046	17615	295	355
250 (37)	0.1411	0.18	0.0143	0.1476	0.574	8.3005	0.111 + j0.734	0.056 + j0.045	22019	318	360

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services