

Cable-in-Conduit (CIC) AL 25kV UD Primary EPEC 13.5



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductors: 25kV AL 100% TRXLPE Full Neutral LLDPE JKT
- Conduit: High-Density Polyethylene (HDPE)

APPLICATIONS AND FEATURES:

Southwire's SIMpull® CIC has been utilized by end users in various applications, including the US Department of Transportation (DOT), the US Department of Energy (DOE), commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. Manufactured by continuously extruding HDPE loosely around the cable assembly with no adhesion between the conduit and the cable, thus leaving the cables free in the conduit. Lubrication is applied to the cable, allowing for cables to be pulled out and replaced if necessary.

SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM D3485 Standard Specification for Coilable High Density Polyethylene (HDPE) Cable in Conduit (CIC)
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- NEMA TC-7 Smooth-Wall Coilable Electrical Polyethylene Conduit

SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CABLE IN CONDUIT HDPE 2" EPEC-13.5 NEMA TC 7 / SDR13.5 ASTM F2160 (NESC)
{MMM/DD/YYYY} {MACH/SHFT/OP}



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: April 8, 2024, 6:37 p.m. UTC REVISION: 1.000.046

Table 1 – Physical and Electrical Data

Stock Number	Description	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
		inch	inch	inch	inch	inch	lb		lb/1000ft
630139	1 x 1/0 AWG Sol AL 260 mil 25kV TR-XLPE Full Neutral Primary UD	2.00	2.375	0.176	2.002	26	2585	Red	1244

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Cable Specification

Stock Number	Cable Specification
630139	SPEC 81141

Cell Classification for HDPE Conduit

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

- (PE436580C-BK), (PE436580E-Colors)

CIC Labor
Saving
Calculator

