


35kV CU 133% EPR (EAM) One-Third Neutral LLDPE

Single Conductor, 420 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 133% Insulation Level, One-third Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



CONSTRUCTION:

- Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
- Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
- Insulation:** 420 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 133% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Concentric Neutral:** Helically applied soft drawn bare copper one-third concentric neutral
- Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 35kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 35000 VOLTS EPR INSULATION 420 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:38 p.m. UTC REVISION: 1.000.001

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	4/0 (19)	0.512	1.390	420	1.500	18x14	0.146	75	1.778	1957	14.2	1692
TBA	250 (37)	0.558	1.444	420	1.554	21x14	0.125	75	1.832	2170	14.7	2000
TBA	350 (37)	0.661	1.547	420	1.687	29x14	0.090	75	1.965	2733	15.7	2800
TBA	500 (37)	0.789	1.675	420	1.815	26x12	0.063	75	2.127	3475	17.0	4000
TBA	750 (61)	0.968	1.864	420	2.004	25x10	0.041	75	2.358	4738	18.9	6000
TBA	1000 (61)	1.117	2.013	420	2.173	32x10	0.032	75	2.527	5929	20.2	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω /1000ft	Ω /1000ft	M Ω *1000ft	Ω /1000ft	A/1000ft	W/1000ft	Ω /1000ft	Ω /1000ft	Amp	Amp	Amp
4/0 (19)	0.051	0.065	0.052	0.050	0.224	17.20	0.119 + j0.729	0.065 + j0.051	6277	300	360
250 (37)	0.043	0.056	0.049	0.049	0.235	18.05	0.110 + j0.726	0.056 + j0.049	7323	328	
350 (37)	0.031	0.041	0.044	0.047	0.263	20.20	0.095 + j0.719	0.041 + j0.047	10113	400	460
500 (37)	0.022	0.030	0.039	0.044	0.297	22.81	0.084 + j0.711	0.030 + j0.045	14406	470	525
750 (61)	0.014	0.023	0.034	0.042	0.341	26.19	0.077 + j0.701	0.023 + j0.042	22019	560	590
1000 (61)	0.011	0.019	0.030	0.040	0.380	29.18	0.073 + j0.695	0.019 + j0.040	28184		

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	4/0 (19)	13.00	35.31	10.67	38.10	18x14	0.48	1.91	45.16	2912	360.68	7529
TBA	250 (37)	14.17	36.68	10.67	39.47	21x14	0.41	1.91	46.53	3229	373.38	8900
TBA	350 (37)	16.79	39.29	10.67	42.85	29x14	0.30	1.91	49.91	4067	398.78	12460
TBA	500 (37)	20.04	42.55	10.67	46.10	26x12	0.21	1.91	54.03	5171	431.80	17800
TBA	750 (61)	24.59	47.35	10.67	50.90	25x10	0.13	1.91	59.89	7051	480.06	26700
TBA	1000 (61)	28.37	51.13	10.67	55.19	32x10	0.10	1.91	64.19	8823	513.08	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
4/0 (19)	0.1673	0.21	0.0158	0.1640	0.735	56.4304	0.119 + j0.729	0.065 + j0.051	6277	300	360
250 (37)	0.1411	0.18	0.0149	0.1608	0.771	59.2192	0.110 + j0.726	0.056 + j0.049	7323	328	
350 (37)	0.1017	0.13	0.0134	0.1542	0.863	66.2730	0.095 + j0.719	0.041 + j0.047	10113	400	460
500 (37)	0.0722	0.10	0.0119	0.1444	0.974	74.8360	0.084 + j0.711	0.030 + j0.045	14406	470	525
750 (61)	0.0459	0.08	0.0104	0.1378	1.119	85.9252	0.077 + j0.701	0.023 + j0.042	22019	560	590
1000 (61)	0.0361	0.06	0.0091	0.1312	1.247	95.7349	0.073 + j0.695	0.019 + j0.040	28184		

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator

