

## HVTECK AL 3/C 115NLEPR TS PVC AIA PVC 8kV 100% CSA

3 Conductor, 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 100% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Filler:** Interstices filled with non-hydroscooping/non-wicking fillers
7. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
8. **Binder:** Polypropylene tape
9. **Inner Jacket:** PVC inner jacket
10. **Armour:** Aluminum Interlocked Armour (AIA)
11. **Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 8kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

### SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable



- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

**SAMPLE PRINT LEGEND:**

(CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CPT AL 115 NLEPR AIA 8kV 100% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

**Table 1 – Weights and Measurements**

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground Size	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/ Kcmil	No.	inch	inch	mil	inch	AWG	mil	inch	mil	inch	lb/1000ft
3/0	19	0.422	0.690	115	0.750	6	110	2.239	60	2.359	2284

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

**Table 2 – Electrical and Engineering Data**

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
3/0	16.5	3020	0.105	0.133	0.020	0.035	0.509 + j0.438	0.133 + j0.034	2354	234	260

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

**Table 3 – Weights and Measurements (Metric)**

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground Size	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/ Kcmil	No.	mm	mm	mm	mm	AWG	mm	mm	mm	mm	kg/km
3/0	19	10.72	17.53	2.92	19.05	6	2.79	56.87	1.52	59.92	3399

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM



**Table 4 – Electrical and Engineering Data (Metric)**

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
3/0	419.10	13439	0.3445	0.44	0.0061	0.1148	0.509 + j0.438	0.133 + j0.034	2354	234	260

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

