

CU Compressed 2.4kV NLEPR Insulation PVC Jacket. MV 90

Type MV-90 Single Conductor Copper, No Lead Ethylene Propylene Rubber (NL-EPR) Polyvinyl Chloride (PVC) Jacket



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
- Conductor Shield:** Semi-conducting cross-linked copolymer
- Insulation:** No Lead Ethylene Propylene Rubber (NL-EPR)
- Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 2.4KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-96-659 (NEMA WC 71) 2001-5000 V Nonshielded Cables
- CT USE Sizes 1/0 AWG and Larger
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE{R} POWER CABLE {UL} XX AWG CU XXX MILS NL-EPR 2400V NONSHIELDED MV-90 SUN. RES. FOR CT USE {NESC}

Table 1 – Weights and Measurements

607283	350	37	0.661	0.965	120	1.207	1080	1531	2800	9.6	3.5
--------	-----	----	-------	-------	-----	-------	------	------	------	-----	-----

All dimensions are nominal and subject to normal manufacturing tolerances





◇ Cable marked with this symbol is a standard stock item
 * Conduit size based on 3 phase 40% fill-factor without ground

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
350	0.031	0.041	0.0355	385/415	550/615

* NEC ampacities are based on:
 * For Duct: Table 310.60(C)(11) Detail 1.
 * For Free Air: Table 310.60(C)(3).
 * Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

Cables With SIMpull Jacket

Size AWG	Stock Code
#2	607457
500	601484

