



CU Compressed 2.4kV NLEPR Insulation 100% IL AIA PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 90 Mils Ethylene Propylene Rubber (EPR) Aluminum Interlocked Armor (AIA), Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 90 Mils Ethylene Propylene Rubber (EPR)
4. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
5. **Filler:** Wax paper filler
6. **Binder:** Polypropylene tape
7. **Armor:** Aluminum Interlocked Armor (AIA)
8. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 2.4KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -40°C for cold bend and cold impact and marked with "LTGG" when CSA listed or dual UL/CSA listed. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-96-659 (NEMA WC 71) 2001-5000 V Nonshielded Cables
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661





SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE® POWER CABLE {UL} 3/C XXX AWG CU 90 MILS NL-EPR 2400V NONSHIELDED GW 1 X X AWG CU MV-105 FOR CT USE - SUN. RES. - FOR DIRECT BURIAL - WET & DRY LOC. {NESC}

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch
890086◇	2	7	0.282	0.495	1 x 6	1.283	55	1.393	702	1278	1592	9.8
606467	1/0	19	0.361	0.580	1 x 4	1.567	65	1.699	1118	1918	2534	11.9
552212	2/0	19	0.405	0.625	1 x 4	1.664	65	1.796	1375	2258	3194	12.6
552213	4/0	19	0.512	0.715	1 x 3	1.859	65	1.991	2143	3118	5078	13.9
551526◇	350	37	0.661	0.865	1 x 2	2.183	80	2.349	3481	4805	8400	16.4
890645◇	500	37	0.789	0.990	1 x 1	2.453	80	2.619	4938	6483	12000	18.3
552256	750	61	0.968	1.205	1 x 1/0	2.919	85	3.089	7345	9230	18000	21.6

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
2	0.162	0.204	0.035	0.186 + j0.02	0.196 + j0.029	135/145	140/154
1/0	0.102	0.128	0.032	0.11 + j0.017	0.12 + j0.026	175/190	185/205
2/0	0.081	0.102	0.032	0.084 + j0.016	0.094 + j0.025	200/220	215/240
4/0	0.051	0.065	0.030	0.047 + j0.015	0.057 + j0.023	265/280	285/320
350	0.031	0.041	0.028	0.023 + j0.013	0.033 + j0.022	355/380	395/440
500	0.022	0.030	0.027	0.012 + j0.012	0.022 + j0.021	430/460	485/545
750	0.014	0.023	0.027	0.005 + j0.011	0.015 + j0.02	530/570	615/685

* Ampacities are based on:

* For Duct: Table 310.60(C)(79) Detail 1.

* For Free Air: Table 310.60(C)(71).

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

* Capacitive Reactance is between Phase-to-Shield.

