

## HVTECK AL 1/C 115TRXLPE TS PVC AIA PVC 5kV 133% CSA

Single Conductor, 115 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
- Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
- Insulation:** 115 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
- Inner Jacket:** PVC inner jacket
- Armour:** Aluminum Interlocked Armour (AIA)
- Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 5kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

### SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)



- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

### SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 115 TRXLPE AIA 5kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

**Table 1 – Weights and Measurements**

| Cond. Size    | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|---------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/<br>Kcmil | No.    | inch                    | inch                     | mil              | inch                            | mil                    | inch             | mil                      | inch       | lb/1000ft      |
| 2             | 7      | 0.268                   | 0.536                    | 115              | 0.596                           | 65                     | 0.968            | 50                       | 1.068      | 537            |
| 1             | 19     | 0.298                   | 0.566                    | 115              | 0.626                           | 65                     | 0.998            | 50                       | 1.098      | 573            |
| 1/0           | 19     | 0.336                   | 0.604                    | 115              | 0.664                           | 65                     | 1.036            | 50                       | 1.136      | 624            |
| 2/0           | 19     | 0.376                   | 0.644                    | 115              | 0.704                           | 80                     | 1.106            | 50                       | 1.206      | 712            |
| 3/0           | 19     | 0.422                   | 0.690                    | 115              | 0.750                           | 80                     | 1.152            | 50                       | 1.252      | 780            |
| 4/0           | 19     | 0.474                   | 0.742                    | 115              | 0.802                           | 80                     | 1.204            | 50                       | 1.304      | 862            |
| 250           | 37     | 0.520                   | 0.796                    | 115              | 0.856                           | 80                     | 1.368            | 50                       | 1.468      | 953            |
| 350           | 37     | 0.615                   | 0.891                    | 115              | 0.951                           | 80                     | 1.463            | 50                       | 1.563      | 1120           |
| 500           | 37     | 0.735                   | 1.011                    | 115              | 1.071                           | 80                     | 1.583            | 60                       | 1.703      | 1387           |
| 750           | 61     | 0.908                   | 1.194                    | 115              | 1.254                           | 80                     | 1.790            | 60                       | 1.910      | 1812           |
| 1000          | 61     | 1.060                   | 1.346                    | 115              | 1.406                           | 80                     | 1.942            | 60                       | 2.062      | 2267           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM



**Table 2 – Electrical and Engineering Data**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Phase Short Circuit Current @ 60Hz | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|------------------------------------|--------------------------------|---|
| AWG/ Kcmil | inch               | lb               | Ω/1000ft             | Ω/1000ft             | MΩ/1000ft                   | Ω/1000ft                   | Ω/1000ft                 | Ω/1000ft                     | Amp                                | Amp                            | Amp                                     |
| 2          | 7.4                | 398              | 0.267                | 0.336                | 0.047                       | 0.053                      | 0.688 + j0.521           | 0.337 + j0.053               | 1846                               | 169                            | 176                                     |
| 1          | 7.6                | 502              | 0.211                | 0.266                | 0.043                       | 0.052                      | 0.621 + j0.503           | 0.267 + j0.05                | 1939                               | 194                            | 198                                     |
| 1/0        | 7.9                | 633              | 0.168                | 0.211                | 0.039                       | 0.050                      | 0.57 + j0.483            | 0.212 + j0.048               | 2057                               | 222                            | 223                                     |
| 2/0        | 8.4                | 798              | 0.133                | 0.167                | 0.036                       | 0.048                      | 0.528 + j0.462           | 0.168 + j0.047               | 2181                               | 255                            | 250                                     |
| 3/0        | 8.7                | 1006             | 0.105                | 0.133                | 0.033                       | 0.047                      | 0.496 + j0.439           | 0.134 + j0.045               | 2323                               | 290                            | 278                                     |
| 4/0        | 9.1                | 1269             | 0.084                | 0.105                | 0.030                       | 0.045                      | 0.469 + j0.416           | 0.106 + j0.043               | 2484                               | 329                            | 309                                     |
| 250        | 10.2               | 1500             | 0.071                | 0.090                | 0.028                       | 0.046                      | 0.451 + j0.392           | 0.091 + j0.044               | 2652                               | 370                            | 347                                     |
| 350        | 10.9               | 2100             | 0.050                | 0.065                | 0.025                       | 0.043                      | 0.424 + j0.355           | 0.066 + j0.042               | 2946                               | 446                            | 402                                     |
| 500        | 11.9               | 3000             | 0.035                | 0.046                | 0.021                       | 0.041                      | 0.398 + j0.315           | 0.047 + j0.039               | 3318                               | 533                            | 451                                     |
| 750        | 13.3               | 4500             | 0.024                | 0.033                | 0.018                       | 0.039                      | 0.37 + j0.264            | 0.034 + j0.037               | 3885                               | 631                            | 500                                     |
| 1000       | 14.4               | 6000             | 0.018                | 0.026                | 0.016                       | 0.037                      | 0.349 + j0.23            | 0.027 + j0.036               | 4356                               | 707                            | 539                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

**Table 3 – Weights and Measurements (Metric)**

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/ Kcmil | No.    | mm                      | mm                       | mm               | mm                              | mm                     | mm               | mm                       | mm         | kg/km          |
| 2          | 7      | 6.81                    | 13.61                    | 2.92             | 15.14                           | 1.65                   | 24.59            | 1.27                     | 27.13      | 799            |
| 1          | 19     | 7.57                    | 14.38                    | 2.92             | 15.90                           | 1.65                   | 25.35            | 1.27                     | 27.89      | 853            |
| 1/0        | 19     | 8.53                    | 15.34                    | 2.92             | 16.87                           | 1.65                   | 26.31            | 1.27                     | 28.85      | 929            |
| 2/0        | 19     | 9.55                    | 16.36                    | 2.92             | 17.88                           | 2.03                   | 28.09            | 1.27                     | 30.63      | 1060           |
| 3/0        | 19     | 10.72                   | 17.53                    | 2.92             | 19.05                           | 2.03                   | 29.26            | 1.27                     | 31.80      | 1161           |
| 4/0        | 19     | 12.04                   | 18.85                    | 2.92             | 20.37                           | 2.03                   | 30.58            | 1.27                     | 33.12      | 1283           |
| 250        | 37     | 13.21                   | 20.22                    | 2.92             | 21.74                           | 2.03                   | 34.75            | 1.27                     | 37.29      | 1418           |
| 350        | 37     | 15.62                   | 22.63                    | 2.92             | 24.16                           | 2.03                   | 37.16            | 1.27                     | 39.70      | 1667           |
| 500        | 37     | 18.67                   | 25.68                    | 2.92             | 27.20                           | 2.03                   | 40.21            | 1.52                     | 43.26      | 2064           |
| 750        | 61     | 23.06                   | 30.33                    | 2.92             | 31.85                           | 2.03                   | 45.47            | 1.52                     | 48.51      | 2697           |
| 1000       | 61     | 26.92                   | 34.19                    | 2.92             | 35.71                           | 2.03                   | 49.33            | 1.52                     | 52.37      | 3374           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM



**Table 4 – Electrical and Engineering Data (Metric)**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Phase Short Circuit Current @ 60Hz | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|------------------------------------|--------------------------------|---|
| AWG/Kcmil  | mm                 | newton           | Ω/km                 | Ω/km                 | MΩ/km                       | Ω/km                       | Ω/1000ft                 | Ω/1000ft                     | Amp                                | Amp                            | Amp                                     |
| 2          | 187.96             | 1771             | 0.8760               | 1.10                 | 0.0143                      | 0.1739                     | 0.688 + j0.521           | 0.337 + j0.053               | 1846                               | 169                            | 176                                     |
| 1          | 193.04             | 2234             | 0.6923               | 0.87                 | 0.0131                      | 0.1706                     | 0.621 + j0.503           | 0.267 + j0.05                | 1939                               | 194                            | 198                                     |
| 1/0        | 200.66             | 2817             | 0.5512               | 0.69                 | 0.0119                      | 0.1640                     | 0.57 + j0.483            | 0.212 + j0.048               | 2057                               | 222                            | 223                                     |
| 2/0        | 213.36             | 3551             | 0.4364               | 0.55                 | 0.0110                      | 0.1575                     | 0.528 + j0.462           | 0.168 + j0.047               | 2181                               | 255                            | 250                                     |
| 3/0        | 220.98             | 4477             | 0.3445               | 0.44                 | 0.0101                      | 0.1542                     | 0.496 + j0.439           | 0.134 + j0.045               | 2323                               | 290                            | 278                                     |
| 4/0        | 231.14             | 5647             | 0.2756               | 0.34                 | 0.0091                      | 0.1476                     | 0.469 + j0.416           | 0.106 + j0.043               | 2484                               | 329                            | 309                                     |
| 250        | 259.08             | 6675             | 0.2329               | 0.30                 | 0.0085                      | 0.1509                     | 0.451 + j0.392           | 0.091 + j0.044               | 2652                               | 370                            | 347                                     |
| 350        | 276.86             | 9345             | 0.1640               | 0.21                 | 0.0076                      | 0.1411                     | 0.424 + j0.355           | 0.066 + j0.042               | 2946                               | 446                            | 402                                     |
| 500        | 302.26             | 13350            | 0.1148               | 0.15                 | 0.0064                      | 0.1345                     | 0.398 + j0.315           | 0.047 + j0.039               | 3318                               | 533                            | 451                                     |
| 750        | 337.82             | 20025            | 0.0787               | 0.11                 | 0.0055                      | 0.1280                     | 0.37 + j0.264            | 0.034 + j0.037               | 3885                               | 631                            | 500                                     |
| 1000       | 365.76             | 26700            | 0.0591               | 0.09                 | 0.0049                      | 0.1214                     | 0.349 + j0.23            | 0.027 + j0.036               | 4356                               | 707                            | 539                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

