

HVTECK AL 1/C 140TRXLPE TS PVC AIA PVC 8kV 133% CSA

Single Conductor, 140 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
- Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
- Insulation:** 140 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
- Inner Jacket:** PVC inner jacket
- Armour:** Aluminum Interlocked Armour (AIA)
- Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 8kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)



- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 140 TRXLPE AIA 8kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
	AWG/ Kcmil	No.	inch	inch	mil	inch	mil	inch	mil	inch	lb/1000ft
TBA	2	7	0.268	0.586	140	0.646	65	1.018	50	1.118	585
TBA	1	19	0.298	0.616	140	0.676	80	1.078	50	1.178	657
TBA	1/0	19	0.336	0.654	140	0.714	80	1.116	50	1.216	709
TBA	2/0	19	0.376	0.694	140	0.754	80	1.156	50	1.256	766
TBA	3/0	19	0.422	0.740	140	0.800	80	1.202	50	1.302	837
TBA	4/0	19	0.474	0.792	140	0.852	80	1.364	50	1.464	930
TBA	250	37	0.520	0.846	140	0.906	80	1.418	50	1.518	1014
TBA	350	37	0.615	0.941	140	1.001	80	1.513	60	1.633	1216
672085	500	34	0.735	1.084	140	1.144	80	1.656	60	1.776	1479
TBA	750	61	0.908	1.244	140	1.304	80	1.840	60	1.960	1890
TBA	1000	61	1.060	1.396	140	1.456	80	1.992	60	2.112	2355

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM



Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	7.8	398	0.267	0.336	0.053	0.055	0.693 + j0.497	0.337 + j0.054	2001	169	176
1	8.2	502	0.211	0.266	0.049	0.053	0.625 + j0.479	0.267 + j0.052	2094	194	198
1/0	8.5	633	0.168	0.211	0.045	0.051	0.572 + j0.46	0.212 + j0.05	2212	222	223
2/0	8.7	798	0.133	0.167	0.041	0.049	0.53 + j0.44	0.168 + j0.048	2336	255	250
3/0	9.1	1006	0.105	0.133	0.038	0.048	0.497 + j0.419	0.134 + j0.046	2478	290	278
4/0	10.2	1269	0.084	0.105	0.034	0.048	0.467 + j0.396	0.106 + j0.046	2639	329	309
250	10.6	1500	0.071	0.090	0.033	0.046	0.45 + j0.375	0.091 + j0.045	2806	370	347
350	11.4	2100	0.050	0.065	0.028	0.044	0.421 + j0.339	0.066 + j0.043	3101	446	402
500	12.4	3000	0.035	0.046	0.024	0.042	0.394 + j0.301	0.047 + j0.04	3473	533	451
750	13.7	4500	0.024	0.033	0.021	0.039	0.366 + j0.253	0.034 + j0.038	4040	631	500
1000	14.7	6000	0.018	0.026	0.018	0.038	0.345 + j0.221	0.027 + j0.036	4511	707	539

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	mm	mm	mm	mm	mm	mm	mm	mm	kg/km
TBA	2	7	6.81	14.88	3.56	16.41	1.65	25.86	1.27	28.40	871
TBA	1	19	7.57	15.65	3.56	17.17	2.03	27.38	1.27	29.92	978
TBA	1/0	19	8.53	16.61	3.56	18.14	2.03	28.35	1.27	30.89	1055
TBA	2/0	19	9.55	17.63	3.56	19.15	2.03	29.36	1.27	31.90	1140
TBA	3/0	19	10.72	18.80	3.56	20.32	2.03	30.53	1.27	33.07	1246
TBA	4/0	19	12.04	20.12	3.56	21.64	2.03	34.65	1.27	37.19	1384
TBA	250	37	13.21	21.49	3.56	23.01	2.03	36.02	1.27	38.56	1509
TBA	350	37	15.62	23.90	3.56	25.43	2.03	38.43	1.52	41.48	1810
672085	500	34	18.67	27.53	3.56	29.06	2.03	42.06	1.52	45.11	2201
TBA	750	61	23.06	31.60	3.56	33.12	2.03	46.74	1.52	49.78	2813
TBA	1000	61	26.92	35.46	3.56	36.98	2.03	50.60	1.52	53.64	3505

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	MΩ/km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	198.12	1771	0.8760	1.10	0.0162	0.1804	0.693 + j0.497	0.337 + j0.054	2001	169	176
1	208.28	2234	0.6923	0.87	0.0149	0.1739	0.625 + j0.479	0.267 + j0.052	2094	194	198
1/0	215.90	2817	0.5512	0.69	0.0137	0.1673	0.572 + j0.46	0.212 + j0.05	2212	222	223
2/0	220.98	3551	0.4364	0.55	0.0125	0.1608	0.53 + j0.44	0.168 + j0.048	2336	255	250
3/0	231.14	4477	0.3445	0.44	0.0116	0.1575	0.497 + j0.419	0.134 + j0.046	2478	290	278
4/0	259.08	5647	0.2756	0.34	0.0104	0.1575	0.467 + j0.396	0.106 + j0.046	2639	329	309
250	269.24	6675	0.2329	0.30	0.0101	0.1509	0.45 + j0.375	0.091 + j0.045	2806	370	347
350	289.56	9345	0.1640	0.21	0.0085	0.1444	0.421 + j0.339	0.066 + j0.043	3101	446	402
500	314.96	13350	0.1148	0.15	0.0073	0.1378	0.394 + j0.301	0.047 + j0.04	3473	533	451
750	347.98	20025	0.0787	0.11	0.0064	0.1280	0.366 + j0.253	0.034 + j0.038	4040	631	500
1000	373.38	26700	0.0591	0.09	0.0055	0.1247	0.345 + j0.221	0.027 + j0.036	4511	707	539

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

