

HVTECK AL 1/C 345NLEPR CB PVC AIA PVC 35kV 100% CSA

Single Conductor, 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 100% Insulation Level, Concentric Bond, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
- Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
- Insulation:** 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Concentric Shield:** Concentrically applied copper bond / shield wires. Complies with greater than the minimum requirement as per Table 44, CSA Standard C68.10 and Table 16A, Canadian Electrical Code Part 1
- Neutral Separator:** Mylar tape
- Inner Jacket:** PVC inner jacket
- Armour:** Aluminum Interlocked Armour (AIA)
- Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 35kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)



- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 345 NLEPR AIA 35kV 100% INS LEVEL CB [No. x SIZE] AWG SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/ Kcmil	No.	inch	inch	mil	inch	No. x AWG	mil	inch	mil	inch	lb/1000ft
1/0	19	0.336	1.064	345	1.124	7 x 14	80	1.774	60	1.894	1357
2/0	19	0.376	1.104	345	1.164	11 x 14	80	1.814	60	1.934	1481
3/0	19	0.422	1.150	345	1.210	11 x 14	80	1.860	60	1.980	1655
4/0	19	0.474	1.202	345	1.262	11 x 14	80	1.912	60	2.032	1757
250	37	0.520	1.256	345	1.316	13 x 14	80	1.966	60	2.086	1887
350	37	0.615	1.351	345	1.411	17 x 14	110	2.121	60	2.241	2267
500	37	0.735	1.471	345	1.531	21 x 14	110	2.241	60	2.361	2611
750	61	0.908	1.654	345	1.714	17 x 12	110	2.458	75	2.608	3245

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	13.2	633	0.168	0.211	0.060	0.061	0.193 + j0.035	0.199 + j0.043	5458	221	219
2/0	13.5	798	0.133	0.167	0.056	0.059	0.149 + j0.033	0.155 + j0.041	8577	253	246
3/0	13.8	1006	0.105	0.133	0.052	0.057	0.115 + j0.031	0.121 + j0.04	8577	288	275
4/0	14.2	1269	0.084	0.105	0.048	0.055	0.087 + j0.03	0.093 + j0.038	8577	327	305
250	14.6	1500	0.071	0.090	0.046	0.054	0.072 + j0.028	0.078 + j0.036	10137	367	343
350	15.6	2100	0.050	0.065	0.040	0.051	0.047 + j0.026	0.053 + j0.034	13256	443	399
500	16.5	3000	0.035	0.046	0.036	0.048	0.028 + j0.024	0.034 + j0.032	16376	529	451
750	18.2	4500	0.024	0.033	0.031	0.046	0.015 + j0.021	0.022 + j0.03	21062	633	505



* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/Kcmil	No.	mm	mm	mm	mm	No. x AWG	mm	mm	mm	mm	kg/km
1/0	19	8.53	27.03	8.76	28.55	7 x 14	2.03	45.06	1.52	48.11	2019
2/0	19	9.55	28.04	8.76	29.57	11 x 14	2.03	46.08	1.52	49.12	2204
3/0	19	10.72	29.21	8.76	30.73	11 x 14	2.03	47.24	1.52	50.29	2463
4/0	19	12.04	30.53	8.76	32.05	11 x 14	2.03	48.56	1.52	51.61	2615
250	37	13.21	31.90	8.76	33.43	13 x 14	2.03	49.94	1.52	52.98	2808
350	37	15.62	34.32	8.76	35.84	17 x 14	2.79	53.87	1.52	56.92	3374
500	37	18.67	37.36	8.76	38.89	21 x 14	2.79	56.92	1.52	59.97	3886
750	61	23.06	42.01	8.76	43.54	17 x 12	2.79	62.43	1.91	66.24	4829

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	MΩ/km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	335.28	2817	0.5512	0.69	0.0183	0.2001	0.193 + j0.035	0.199 + j0.043	5458	221	219
2/0	342.90	3551	0.4364	0.55	0.0171	0.1936	0.149 + j0.033	0.155 + j0.041	8577	253	246
3/0	350.52	4477	0.3445	0.44	0.0158	0.1870	0.115 + j0.031	0.121 + j0.04	8577	288	275
4/0	360.68	5647	0.2756	0.34	0.0146	0.1804	0.087 + j0.03	0.093 + j0.038	8577	327	305
250	370.84	6675	0.2329	0.30	0.0140	0.1772	0.072 + j0.028	0.078 + j0.036	10137	367	343
350	396.24	9345	0.1640	0.21	0.0122	0.1673	0.047 + j0.026	0.053 + j0.034	13256	443	399
500	419.10	13350	0.1148	0.15	0.0110	0.1575	0.028 + j0.024	0.034 + j0.032	16376	529	451
750	462.28	20025	0.0787	0.11	0.0094	0.1509	0.015 + j0.021	0.022 + j0.03	21062	633	505

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

