

AL 600V XLPE Insulation. XHHW-2 Silicone Free

Power Cable 600 or 1000 Volt Single Conductor Aluminum, Cross Linked Polyethylene (XLPE) insulation XHHW-2




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2

APPLICATIONS AND FEATURES:

Southwire's 600 or 1000 Volt power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- CT USE Sizes 1/0 AWG and Larger
- VW-1 (Vertical-Wire) Flame Test

SAMPLE PRINT LEGEND:

SOUTHWIRE E30117 MASTER-DESIGN {UL} XXX AWG 8000 COMPACT AL.--- TRIPLE E ALLOY AA8176 TYPE XHHW-2 VW-1 FOR CT USE SUN. RES. 600V OR 1000V {YYYY} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET



Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Insul. Thickness	Approx. OD	Aluminum Weight	Approx. Weight
	AWG/Kcmil	No. of Strands	inch	mil	inch	lb/1000ft	lb/1000ft
560397	1/0	10	0.336	55	0.458	99	144
TBA	2/0	19	0.376	55	0.486	125	163
560395	3/0	16	0.422	55	0.539	158	211
560361	4/0	19	0.474	55	0.591	199	258
560362	250	22	0.520	65	0.660	235	313
562832	300	35	0.569	65	0.707	282	365
560363	350	35	0.615	65	0.756	329	421
563044	600	58	0.812	80	0.973	565	707
560381	750	58	0.908	80	1.080	706	870
560382	1000	58	1.060	80	1.228	942	1129

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 60°C	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
560397	1/0	1.8	633	0.168	0.201	0.044	100	120	135
TBA	2/0	1.9	798	0.133	0.160	0.043	115	135	150
560395	3/0	2.1	1006	0.105	0.126	0.042	130	155	175
560361	4/0	2.3	1269	0.084	0.100	0.041	150	180	205
560362	250	2.6	1500	0.071	0.086	0.041	170	205	230
562832	300	2.8	1800	0.059	0.071	0.041	195	230	260
560363	350	3.0	2100	0.050	0.062	0.040	210	250	280
563044	600	3.8	3600	0.029	0.037	0.039	285	340	385
560381	750	5.4	4500	0.024	0.031	0.038	320	385	435
560382	1000	6.1	6000	0.018	0.025	0.037	375	445	500

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Inductive Reactance is based on non-ferrous conduit with one diameter spacing.

