

CU 600/1000V XLPE Insulation Thermoplastic LSZH-TP. XHHW-2

Type TC-ER Power Cable 600Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket with 1 Bare CU Ground.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
- Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (cable size 8 & 6 has insulated green ground)
- Filler:** Paper filler (cable size 8 & 6 uses Polypropylene filler)
- Binder:** Polyester flat thread binder tape for cable sizes larger than 2 AWG
- Overall Jacket:** Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type TC-ER power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- NFPA 130 Standard for Fixed Guideway Transit and Passenger Rail Systems (500kcmil & Larger)

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE{R} MASTER-DESIGN {UL} XXX AWG CU 3/C TYPE TC-ER XHHW-2 CDRS GW 1 X X AWG CU SOLONON{R} 90{D}C JACKET SUN RES OIL RES I FOR DIRECT BURIAL 600V



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/ Kcmil		No. of Strands	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft
561568	8	3	7	0.141	45	1 x 10 GG	45	0.700	186	339
561567	6	3	7	0.177	45	1 x 8 GG	45	0.795	297	480
551378	2	3	7	0.282	45	1 x 6	60	0.980	702	979
TBA	1	3	19	0.322	55	1 x 6	80	1.105	863	1179
TBA	1/0	3	19	0.361	55	1 x 6	80	1.189	1067	1416
561564	2/0	3	19	0.405	55	1 x 6	80	1.302	1326	1719
565815	3/0	3	19	0.456	55	1 x 4	80	1.406	1699	2132
959718	4/0	3	19	0.512	55	1 x 4	80	1.531	2109	2615
TBA	250	3	37	0.558	65	1 x 4	80	1.658	2466	3041
TBA	350	3	37	0.661	65	1 x 3	110	1.940	3436	4233
564938	500	3	37	0.789	65	1 x 2	110	2.183	4884	5745
552362	500	3	37	0.789	65	3 x 6	110	2.233	4923	5965
TBA	750	3	61	0.968	80	1 x 1	110	2.668	7270	8572

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 60°C	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/ Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
561568	8	3	2.8	396	0.653	0.786	0.052	40	50	55
561567	6	3	3.1	629	0.411	0.495	0.051	55	65	75
551378	2	3	3.9	1592	0.162	0.195	0.045	95	115	130
TBA	1	3	5.5	2008	0.128	0.154	0.046	110	130	145
TBA	1/0	3	5.9	2534	0.102	0.122	0.044	125	150	170
561564	2/0	3	6.5	3194	0.081	0.097	0.043	145	175	195
565815	3/0	3	7.0	4027	0.064	0.078	0.042	165	200	225
959718	4/0	3	7.6	5078	0.051	0.062	0.041	195	230	260
TBA	250	3	8.2	6000	0.043	0.053	0.041	215	255	290
TBA	350	3	9.7	8400	0.031	0.039	0.040	260	310	350
564938	500	3	13.0	10000	0.022	0.029	0.039	320	380	430
552362	500	3	13.3	10000	0.022	0.029	0.039	320	380	430
TBA	750	3	16.0	10000	0.014	0.022	0.038	400	475	535

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

