



# Southwire® Machine Flex® Power PVC THHN

90°C Wet or Dry. 600 Volts. Flexible Stranded Copper Conductor. PVC Insulation and Nylon Jacket (THHN/THWN-2). Oil & Gasoline Resistant. Sunlight Resistant. Rated UL VW-1 and CSA FT1 & FT4 Flame Resistant.



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** 8 - 4/0 AWG: Class K, Flexible stranded bare copper. 250 - 750 kcmil: Class I, Flexible stranded bare copper
2. **Insulation:** Polyvinyl Chloride (PVC) with Nylon sheath

## APPLICATIONS AND FEATURES:

Southwire's Machine Flex® power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 150°C for short circuit conditions. 1/0 AWG & Larger rated for CT use.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 758 Standard for Appliance Wiring Material Style 2463 (80C, 600V)
- UL 1063 Machine Tool Wiring (MTW)
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661





**SAMPLE PRINT LEGEND:**

**8AWG-1AWG**

SOUTHWIRE #P# (UL) 1 AWG (42.406 mm<sup>2</sup>) CU TYPE THHN/THWN-2 600V 90(D)C DRY/90(D)C WET PRI/GRI VW-1 OR AWM [Applicable Styles] OR MTW SUN RES --- (CSA) T90 NYLON OR TWN75 FT1 FT4 --- CE RoHS-2 Made in USA. [SEQUENTIAL FOOTAGE MARKS]

**1/0 AWG - 500 KCMIL**

SOUTHWIRE #P# (UL) 500 KCMIL (253.35mm<sup>2</sup>) CU TYPE THHN/THWN-2 600V 90(D)C DRY/90(D)C WET PRI/GRI VW-1 FOR CT USE OR AWM [Applicable Styles] OR MTW SUN RES --- (CSA) T90 NYLON OR TWN75 FT1 FT4 --- CE RoHS-2 Made in USA. [SEQUENTIAL FOOTAGE MARKS]

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Insul. Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil	No. of Strands	inch	mil	inch	lb/1000ft	lb/1000ft
TBA	8	168	0.153	35	0.223	52	62
TBA	6	273	0.190	35	0.264	83	98
672867	4	413	0.235	50	0.335	130	153
664229	3	525	0.270	50	0.366	169	197
TBA	2	665	0.302	50	0.402	210	243
TBA	1	836	0.329	60	0.449	260	302
677368	1/0	1044	0.400	60	0.520	334	374
TBA	2/0	1330	0.430	60	0.520	381	426
664217	3/0	1672	0.490	60	0.608	535	599
679607	4/0	2109	0.550	60	0.664	676	746
649414	250	627	0.605	70	0.747	763	857
672866	300	741	0.638	70	0.780	929	1024
649415	350	893	0.670	60	0.812	1084	1172
648948	500	1221	0.858	70	0.998	1514	1641
649416	600	1480	0.963	70	1.127	1859	2033
649549◇	750	1850	1.094	80	1.258	2367	2569
674459	1000	2516	1.190	80	1.350	3045	3255

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item





**Table 2 – Electrical and Engineering Data**

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
TBA	8	0.8	132	0.715	0.861	0.052	50	55
TBA	6	1.0	209	0.450	0.541	0.051	65	75
672867	4	1.3	333	0.282	0.340	0.048	85	95
664229	3	1.6	420	0.226	0.272	0.047	100	115
TBA	2	1.6	530	0.179	0.216	0.045	115	130
TBA	1	1.6	669	0.137	0.164	0.046	130	145
677368	1/0	2.0	844	0.113	0.136	0.044	150	170
TBA	2/0	2.0	1064	0.090	0.108	0.043	175	195
664217	3/0	2.4	1342	0.072	0.087	0.042	200	225
679607	4/0	2.6	1692	0.057	0.069	0.041	230	260
649414	250	2.9	2000	0.047	0.057	0.041	255	290
672866	300	3.1	2400	0.039	0.048	0.041	285	320
649415	350	3.2	2800	0.033	0.042	0.040	310	350
648948	500	3.9	4000	0.023	0.031	0.039	380	430
649416	600	5.6	4800	0.019	0.027	0.039	420	475
649549◇	750	6.2	6000	0.016	0.024	0.038	475	535
674459	1000	6.7	8000	0.012	0.020	0.037	545	615

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

† Ampacities have been adjusted for more than Three Current-Carrying Conductors.

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

**Stock Codes and Colors**

Size	BLACK	BROWN	ORANGE	YELLOW	GRAY	GREEN/YELLOW	GREEN	RED
#4	672867	TBA	TBA	TBA	TBA	TBA	674667◇	TBA
#3	TBA	TBA	TBA	TBA	TBA	TBA	664229	TBA
#2	TBA	TBA	TBA	TBA	TBA	TBA	TBA	TBA
1/0	TBA	TBA	TBA	TBA	TBA	677368	674668	TBA
3/0	TBA	664217	664220	664223	664226	TBA	TBA	TBA
4/0	679607	TBA	TBA	TBA	TBA	679606	TBA	TBA
250 Kcmil	649414	672218	672217	672219	673792◇	677370	673791◇	TBA
300 Kcmil	672866	674116	674117	674118	674120	TBA	674121	TBA
350 Kcmil	649415◇	674662◇	674664◇	674665◇	674666◇	672017	652964◇	138181
500 Kcmil	648948◇	646978◇	646979◇	646980◇	646981◇	646982◇	677701	TBA
600 Kcmil	649416◇	678431◇	678432◇	678434◇	678435◇	678436	673748	TBA
750 Kcmil	649549	677721	677722	677723	677725	677726	671518	TBA
1000 Kcmil	674459	TBA	TBA	TBA	TBA	TBA	TBA	TBA

◇ Cable marked with this symbol is a standard stock item

