

CU 2000V XLPE Insulation. RHH/RHW-2 PV

Single Conductor Photovoltaic (Type PV) Power Cable 2000 Volt Copper Conductor XLPE Insulation. Sizes 14 AWG through 1000 Kcmil. Heat, Moisture, Sunlight Resistant RoHS. 90°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Stranded bare copper per ASTM B3 and ASTM B8 or ASTM B787
- Insulation:** Cross Linked Polyethylene (XLPE). Colors available upon request.

APPLICATIONS AND FEATURES:

Southwire's 2000 Volt power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 4703 Standard for Photovoltaic Wire
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- VW-1 Vertical-Wire Flame Test (Optional)

SAMPLE PRINT LEGEND:

SOUTHWIRE E316464 {UL} PV WIRE XX AWG (XXX.XX{mm²}) CU 2000V 90{D}C WET OR DRY -40{D}C SUN RES DIRECT BURIAL VW-1 OR RHW-2 2000V --- RoHS {MMM/DD/YYYY}



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2023 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Sept. 23, 2023, 4:37 p.m. UTC REVISION: 1.000.006

Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Strand Count No. of Strands	Diameter Over Conductor inch	Insul. Thickness mil	Approx. OD inch	Copper Weight lb/1000ft	Approx. Weight lb/1000ft
597961	14	19	0.070	75	0.224	13	30
597958	12	19	0.088	75	0.243	20	39
579962	10	19	0.113	75	0.263	32	53
569037*	8	19	0.134	85	0.313	50	79
569039*	6	19	0.169	85	0.349	81	114
569040*	4	19	0.212	85	0.396	128	166
569041*	2	19	0.268	85	0.456	204	250
TBA	1	19	0.298	105	0.508	259	328
569043	1/0	19	0.336	105	0.570	326	396
569044	2/0	19	0.376	105	0.614	426	504
569045	3/0	19	0.422	105	0.664	518	604
569047	4/0	19	0.474	105	0.720	655	752
679559	250	37	0.520	120	0.782	772	897
653096	300	37	0.611	120	0.851	926	1052
590138	350	37	0.615	120	0.901	1080	1215
578324	500	37	0.735	120	1.006	1543	1685
672530	600	61	0.812	135	1.136	1852	2042
TBA	750	61	0.908	135	1.178	2316	2546
TBA	1000	61	1.060	135	1.330	3086	3350

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item



Table 2 – Electrical and Engineering Data






Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 60° C	Allowable Ampacity At 75° C	Allowable Ampacity At 90° C
	AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
597961	14	1.8	33	2.631	3.423	0.058	15	20	25
597958	12	1.9	52	1.630	2.002	0.054	20	25	30
579962	10	2.1	83	1.020	1.250	0.050	30	35	40
569037*	8	2.5	132	0.654	0.787	0.052	40	50	55
569039*	6	2.8	210	0.411	0.495	0.051	55	65	75
569040*	4	3.2	334	0.258	0.310	0.048	70	85	95
569041*	2	3.6	531	0.162	0.195	0.045	95	115	130
TBA	1	4.1	670	0.128	0.154	0.046	110	130	145
569043	1/0	4.6	845	0.102	0.122	0.044	125	150	170
569044	2/0	4.9	1065	0.081	0.097	0.043	145	175	195
569045	3/0	5.3	1342	0.064	0.078	0.042	165	200	225
569047	4/0	5.8	1693	0.051	0.062	0.041	195	230	260
679559	250	6.2	2000	0.043	0.053	0.041	215	255	290
653096	300	6.8	2400	0.036	0.047	0.029	240	285	320
590138	350	7.2	2800	0.031	0.039	0.040	260	310	350
578324	500	8.0	4000	0.022	0.029	0.039	320	380	430
672530	600	9.1	4800	0.018	0.025	0.039	350	420	475
TBA	750	9.4	6000	0.014	0.022	0.038	400	475	535
TBA	1000	10.6	8000	0.011	0.018	0.037	455	545	615

Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

Inductive Reactance is based on non-ferrous conduit with one diameter spacing.






*VW-1 Rated

Stock Code Colors

Size	Black	White	Red	Green	Green/Yellow
AWG/Kcmil					
14	597961				
12	597958	596376	596377		
10	579962	583665	583687		
1/0	569043				677562
2/0	569044				
3/0	569045				
4/0	569047				
250	679559				
300	653096	599400	599401		
350	590138				
500	578324				
600	672530				



Stock Code Colors (VW-1)

Size	Black	White	Red	Green	Green/Yellow
AWG/Kcmil					
10	568110		577645		
8	569037	585080	589110		
6	569039		671956	585840	
4	569040	673880		653094	
2	569041				

