

## CU 2000V XLPE Insulation Three Grounds Cu Tape Shield PVC Jacket. RHH/RHW-2 Variable Frequency Drive (VFD)

Type TC-ER VFD Power Cable 2000 Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation RHH/RHW-2 Polyvinyl Chloride (PVC) Jacket with 3 Symmetrical Bare CU Ground 50% Minimum Tape Shield Overlap. Silicone Free



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Insulation:** Cross Linked Polyethylene (XLPE) Type RHH/RHW-2
- Grounding Conductor:** 3 Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Ground size is 100% for sizes 14 - 10 awg and a minimum of 50% of the phase conductor for larger sizes.)
- Filler:** Fillers as needed to make round
- Tape Shield:** 5 mil copper tape shield with a minimum of 50% overlap
- Overall Jacket:** Polyvinyl Chloride (PVC) Jacket. Available in thermoplastic Chlorinated Polyethylene CPE jacket on #4 AWG and larger upon request

### APPLICATIONS AND FEATURES:

Southwire's 2000 Volt Type TC-ER VFD power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Type (TC-ER) per NEC 336.10.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

## SAMPLE PRINT LEGEND:

SOUTHWIRE{R} VFD MASTER-DESIGN {UL} XX AWG 3/C TYPE TC-ER RHH OR RHW-2 CDRS CU GW 3 X XX AWG CU T/S 50% 90{D}C PVC JACKET SUN RES DIRECT BURIAL 2000 VOLTS {YYYY} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET FT4/ IEEE1202 2000 VOLTS

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Dia. Over Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/ Kcmil		No. of Strands	inch	mil	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft
580672◇	14	3	7	0.07	60	3 x 18	0.451	60	0.571	93	202
580685◇	12	3	7	0.088	60	3 x 16	0.486	60	0.606	128	244
580693◇	10	3	7	0.113	60	3 x 14	0.537	60	0.657	183	329
569388◇	8	3	7	0.141	70	3 x 14	0.652	60	0.772	270	456
580701◇	6	3	7	0.177	70	3 x 12	0.723	80	0.883	389	624
569389◇	4	3	7	0.225	70	3 x 12	0.825	80	0.985	547	815
569387◇	2	3	7	0.282	70	3 x 10	0.946	80	1.106	827	1121
644333◇	1/0	3	19	0.361	90	3 x 6	1.220	80	1.380	1373	1858
644334◇	2/0	3	19	0.405	90	3 x 6	1.311	80	1.471	1640	2164
644337◇	3/0	3	19	0.456	90	3 x 5	1.419	80	1.579	2041	2604
644338◇	4/0	3	19	0.512	90	3 x 4	1.506	115	1.736	2542	3202
644339◇	250	3	37	0.558	105	3 x 2	1.665	115	1.895	3150	3995
TBA	300	3	37	0.61	105	3 x 3	1.783	110	2.003	2956	3906
668921	350	3	37	0.661	105	3 x 3	1.879	115	2.109	3981	4969
644340◇	350	3	37	0.661	105	3 x 2	1.879	115	2.109	4110	5098
TBA	400	3	37	0.705	105	3 x 2	1.988	110	2.208	3908	4993
644341◇	500	3	37	0.789	105	3 x 1	2.149	115	2.379	5706	6767
669099	600	3	61	0.865	120	3 x 1	2.409	115	2.639	6673	8025
TBA	750	3	61	0.968	120	3 x 2/0	2.621	140	2.901	7235	9006

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item



**Table 2 – Electrical and Engineering Data**

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	Allowable Ampacity At 60°C	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/ Kcmil		inch	lb	Ω/1000ft	Amp	Amp	Amp
580672◇	14	3	6.9	98	2.631	15	20	25
580685◇	12	3	7.3	156	1.662	20	25	30
580693◇	10	3	7.9	249	1.040	30	35	40
569388◇	8	3	9.3	396	0.653	40	50	55
580701◇	6	3	10.6	629	0.411	55	65	75
569389◇	4	3	11.8	1001	0.258	70	85	95
569387◇	2	3	13.3	1592	0.162	95	115	130
644333◇	1/0	3	16.6	2534	0.102	125	150	170
644334◇	2/0	3	17.7	3194	0.081	145	175	195
644337◇	3/0	3	18.9	4027	0.064	165	200	225
644338◇	4/0	3	20.8	5078	0.051	195	230	260
644339◇	250	3	22.7	6000	0.043	215	255	290
TBA	300	3	24.0	7200	0.036	240	285	320
668921	350	3	25.3	8400	0.031	260	310	350
644340◇	350	3	25.3	8400	0.031	260	310	350
TBA	400	3	26.5	9600	0.027	280	335	380
644341◇	500	3	28.5	100000	0.022	320	380	430
669099	600	3	31.7	100000	0.018	350	420	475
TBA	750	3	34.8	100000	0.014	400	475	535

\* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

**Gland Reference**

[Glands](#)

