

CU 600/1000V XLPE Insulation ARMOR-X[®] PVC Jacket XHHW-2. CT Rated -Sunlight Resistant - For Direct Burial - Silicone Free

Type MC-HL Power Cable 600Volt Four Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Continuous Corrugated Welded Armor - ARMOR-X[®], Polyvinyl Chloride (PVC) Jacket with One Bare CU Ground




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
3. **Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
4. **Filler:** Polypropylene filler
5. **Binder:** Polypropylene tape
6. **Armor:** ARMOR-X[®] Continuous Corrugated Welded Armor
7. **Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type MC-HL ARMOR-X[®] power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, 250°C for short circuit conditions, and -50°C for cold bend. For uses in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Article 501, 502, and 503.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Vertical Tray Flame Test (70,000 Btu/hr) and ICEA T-29-520 - (210,000 Btu/hr)





SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE ARMOR-X[®] {UL} TYPE MC-HL 4/C XXX KCMIL (XXX{mm2}) CU XHHW-2 GW 1 X X AWG 90°C JACKET -40°C SUN. RES. DIR. BUR. FOR CT USE 600V IEEE1202/FT4 -- {CSA} RA90-HL AG14 XLPE -40°C 600V FT4 SR 90°C -- CWC MC -- {NOM}-ANCE Tipo MC XHHW-2 CT FT4

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Dia. Over Armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil		No. of Strands	inch	mil	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft
890527	8	4	7	0.141	45	1 x 10	0.840	50	0.946	238	476
890528	6	4	7	0.177	45	1 x 8	0.920	50	1.026	378	649
890529	4	4	7	0.225	45	1 x 8	1.060	50	1.166	569	918
890530	2	4	7	0.282	45	1 x 6	1.220	60	1.326	909	1295
890531	1/0	4	19	0.361	55	1 x 6	1.470	60	1.576	1399	1948
890532	2/0	4	19	0.405	55	1 x 6	1.540	60	1.666	1790	2436
582265	3/0	4	19	0.456	55	1 x 4	1.760	60	1.886	2223	2954
890533	4/0	4	19	0.512	55	1 x 4	1.845	60	1.971	2769	3536
890534	250	4	37	0.558	65	1 x 4	2.040	60	2.166	3248	4278
890535	350	4	37	0.661	65	1 x 3	2.290	75	2.448	4530	5741
890536	500	4	37	0.789	65	1 x 2	2.670	75	2.828	6443	7980
890537	750	4	61	0.968	80	1 x 1	3.220	85	3.398	9616	12254

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Amp	Amp
890527	8	4	6.6	422	0.653	0.786	0.033	0.052	40	44
890528	6	4	7.2	671	0.411	0.495	0.027	0.051	52	60
890529	4	4	8.2	1068	0.258	0.310	0.022	0.048	68	76
890530	2	4	9.3	1698	0.162	0.195	0.018	0.045	92	104
890531	1/0	4	11.0	2703	0.102	0.122	0.017	0.044	120	136
890532	2/0	4	11.7	3407	0.081	0.097	0.016	0.043	140	156
582265	3/0	4	13.2	4295	0.064	0.078	0.014	0.042	160	180
890533	4/0	4	13.8	5416	0.051	0.062	0.013	0.041	184	208
890534	250	4	15.2	6400	0.043	0.053	0.014	0.041	204	232
890535	350	4	17.1	8960	0.031	0.039	0.012	0.040	248	280
890536	500	4	19.8	12800	0.022	0.029	0.010	0.039	304	344
890537	750	4	23.8	19200	0.014	0.022	0.010	0.038	380	428

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

