

HVTECK AL 1/C 420TRXLPE TS PVC AIA PVC 35kV 133% CSA

Single Conductor, 420 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 420 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Inner Jacket:** PVC inner jacket
7. **Armour:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 35kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)



- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 420 TRXLPE AIA 35kV 133% INS LEVEL 25% TS SUN RES 105° C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/ Kcmil	No.	inch	inch	mil	inch	mil	inch	mil	inch	lb/1000ft
1/0	19	0.336	1.214	420	1.274	80	1.810	60	1.930	1528
2/0	19	0.376	1.254	420	1.314	80	1.850	60	1.970	1697
3/0	19	0.422	1.300	420	1.360	80	1.896	60	2.016	1793
4/0	19	0.474	1.352	420	1.412	80	1.948	60	2.068	1905
250	37	0.520	1.406	420	1.466	80	2.002	60	2.122	2018
350	37	0.615	1.501	420	1.561	110	2.157	60	2.277	2367
500	37	0.735	1.621	420	1.681	110	2.277	75	2.427	2751
750	61	0.908	1.804	420	1.864	110	2.460	75	2.610	3262

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	13.5	633	0.168	0.211	0.087	0.062	0.546 + j0.282	0.212 + j0.06	3947	221	219
2/0	13.7	798	0.133	0.167	0.081	0.060	0.499 + j0.271	0.168 + j0.058	4071	253	246
3/0	14.1	1006	0.105	0.133	0.076	0.058	0.461 + j0.26	0.134 + j0.056	4213	288	275
4/0	14.4	1269	0.084	0.105	0.071	0.056	0.428 + j0.247	0.106 + j0.054	4374	327	305
250	14.8	1500	0.071	0.090	0.067	0.054	0.408 + j0.235	0.091 + j0.052	4542	367	343
350	15.9	2100	0.050	0.065	0.060	0.052	0.373 + j0.216	0.066 + j0.05	4836	443	399
500	16.9	3000	0.035	0.046	0.053	0.049	0.343 + j0.196	0.047 + j0.048	5208	529	451
750	18.2	4500	0.024	0.033	0.046	0.046	0.314 + j0.169	0.034 + j0.044	5775	633	505

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.



Table 3 – Weights and Measurements (Metric)

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Approx. Weight
AWG/ Kcmil	No.	mm	mm	mm	mm	mm	mm	mm	mm	kg/km
1/0	19	8.53	30.84	10.67	32.36	2.03	45.97	1.52	49.02	2274
2/0	19	9.55	31.85	10.67	33.38	2.03	46.99	1.52	50.04	2525
3/0	19	10.72	33.02	10.67	34.54	2.03	48.16	1.52	51.21	2668
4/0	19	12.04	34.34	10.67	35.86	2.03	49.48	1.52	52.53	2835
250	37	13.21	35.71	10.67	37.24	2.03	50.85	1.52	53.90	3003
350	37	15.62	38.13	10.67	39.65	2.79	54.79	1.52	57.84	3522
500	37	18.67	41.17	10.67	42.70	2.79	57.84	1.91	61.65	4094
750	61	23.06	45.82	10.67	47.35	2.79	62.48	1.91	66.29	4854

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	mm	newton	Ω/km	Ω/km	MΩ/km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	342.90	2817	0.5512	0.69	0.0265	0.2034	0.546 + j0.282	0.212 + j0.06	3947	221	219
2/0	347.98	3551	0.4364	0.55	0.0247	0.1969	0.499 + j0.271	0.168 + j0.058	4071	253	246
3/0	358.14	4477	0.3445	0.44	0.0232	0.1903	0.461 + j0.26	0.134 + j0.056	4213	288	275
4/0	365.76	5647	0.2756	0.34	0.0216	0.1837	0.428 + j0.247	0.106 + j0.054	4374	327	305
250	375.92	6675	0.2329	0.30	0.0204	0.1772	0.408 + j0.235	0.091 + j0.052	4542	367	343
350	403.86	9345	0.1640	0.21	0.0183	0.1706	0.373 + j0.216	0.066 + j0.05	4836	443	399
500	429.26	13350	0.1148	0.15	0.0162	0.1608	0.343 + j0.196	0.047 + j0.048	5208	529	451
750	462.28	20025	0.0787	0.11	0.0140	0.1509	0.314 + j0.169	0.034 + j0.044	5775	633	505

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

