

HVTECK AL 3/C 420NLEPR TS PVC AIA PVC 35kV 133% CSA

3 Conductor, 420 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 420 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Filler:** Interstices filled with non-hydroscooping/non-wicking fillers
7. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
8. **Binder:** Polypropylene tape
9. **Inner Jacket:** PVC inner jacket
10. **Armour:** Aluminum Interlocked Armour (AIA)
11. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 35kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable



- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CPT AL 420 NLEPR AIA 35kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Ground Size | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|---------------|--------|-------------------------|--------------------------|------------------|---------------------------------|-------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/ Kcmil | No. | inch | inch | mil | inch | AWG | mil | inch | mil | inch | lb/1000ft |
| 1/0 | 19 | 0.336 | 1.214 | 420 | 1.274 | 6 | 125 | 3.401 | 85 | 3.571 | 4928 |
| 2/0 | 19 | 0.376 | 1.254 | 420 | 1.314 | 6 | 125 | 3.487 | 85 | 3.657 | 5188 |
| 3/0 | 19 | 0.422 | 1.300 | 420 | 1.360 | 6 | 125 | 3.586 | 85 | 3.756 | 5498 |
| 4/0 | 19 | 0.474 | 1.352 | 420 | 1.412 | 6 | 125 | 3.699 | 85 | 3.869 | 5868 |
| 250 | 37 | 0.520 | 1.406 | 420 | 1.466 | 4 | 125 | 3.815 | 85 | 3.985 | 6237 |
| 350 | 37 | 0.615 | 1.501 | 420 | 1.561 | 4 | 125 | 4.020 | 85 | 4.190 | 6969 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Phase Short Circuit Current @ 60Hz | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|---------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|------------------------------------|--------------------------------|---|
| AWG/ Kcmil | inch | lb | Ω/1000ft | Ω/1000ft | MΩ/1000ft | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 1/0 | 24.9 | 1900 | 0.168 | 0.211 | 0.067 | 0.053 | 0.553 + j0.281 | 0.211 + j0.051 | 3947 | 181 | 200 |
| 2/0 | 25.5 | 2395 | 0.133 | 0.167 | 0.062 | 0.051 | 0.505 + j0.27 | 0.167 + j0.049 | 4071 | 208 | 228 |
| 3/0 | 26.2 | 3020 | 0.105 | 0.133 | 0.058 | 0.049 | 0.466 + j0.258 | 0.133 + j0.047 | 4213 | 239 | 258 |
| 4/0 | 27 | 3808 | 0.084 | 0.105 | 0.054 | 0.047 | 0.433 + j0.246 | 0.106 + j0.046 | 4374 | 273 | 292 |
| 250 | 27.8 | 4500 | 0.071 | 0.090 | 0.051 | 0.046 | 0.412 + j0.234 | 0.091 + j0.044 | 4542 | 302 | 321 |
| 350 | 29.3 | 6300 | 0.050 | 0.065 | 0.046 | 0.043 | 0.378 + j0.215 | 0.066 + j0.042 | 4836 | 368 | 385 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.



Table 3 – Weights and Measurements (Metric)

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Ground Size | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|-------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/Kcmil | No. | mm | mm | mm | mm | AWG | mm | mm | mm | mm | kg/km |
| 1/0 | 19 | 8.53 | 30.84 | 10.67 | 32.36 | 6 | 3.18 | 86.39 | 2.16 | 90.70 | 7334 |
| 2/0 | 19 | 9.55 | 31.85 | 10.67 | 33.38 | 6 | 3.18 | 88.57 | 2.16 | 92.89 | 7721 |
| 3/0 | 19 | 10.72 | 33.02 | 10.67 | 34.54 | 6 | 3.18 | 91.08 | 2.16 | 95.40 | 8182 |
| 4/0 | 19 | 12.04 | 34.34 | 10.67 | 35.86 | 6 | 3.18 | 93.95 | 2.16 | 98.27 | 8733 |
| 250 | 37 | 13.21 | 35.71 | 10.67 | 37.24 | 4 | 3.18 | 96.90 | 2.16 | 101.22 | 9282 |
| 350 | 37 | 15.62 | 38.13 | 10.67 | 39.65 | 4 | 3.18 | 102.11 | 2.16 | 106.43 | 10371 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 4 – Electrical and Engineering Data (Metric)

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Phase Short Circuit Current @ 60Hz | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|------------------------------------|--------------------------------|---|
| AWG/Kcmil | mm | newton | Ω/km | Ω/km | MΩ/km | Ω/km | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 1/0 | 632.46 | 8455 | 0.5512 | 0.69 | 0.0204 | 0.1739 | 0.553 + j0.281 | 0.211 + j0.051 | 3947 | 181 | 200 |
| 2/0 | 647.70 | 10658 | 0.4364 | 0.55 | 0.0189 | 0.1673 | 0.505 + j0.27 | 0.167 + j0.049 | 4071 | 208 | 228 |
| 3/0 | 665.48 | 13439 | 0.3445 | 0.44 | 0.0177 | 0.1608 | 0.466 + j0.258 | 0.133 + j0.047 | 4213 | 239 | 258 |
| 4/0 | 685.80 | 16946 | 0.2756 | 0.34 | 0.0165 | 0.1542 | 0.433 + j0.246 | 0.106 + j0.046 | 4374 | 273 | 292 |
| 250 | 706.12 | 20025 | 0.2329 | 0.30 | 0.0155 | 0.1509 | 0.412 + j0.234 | 0.091 + j0.044 | 4542 | 302 | 321 |
| 350 | 744.22 | 28035 | 0.1640 | 0.21 | 0.0140 | 0.1411 | 0.378 + j0.215 | 0.066 + j0.042 | 4836 | 368 | 385 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

