

3/C CU 25kV 320 NLEPR 133% PVC MV-105

Type MV-105 Three Conductor Copper, 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Poly glass tape
9. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 25KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- CSA C22.2 No.230 Tray Cables - Rated TC-ER
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE{R} POWER CABLE MASTER-DESIGN {UL} 3/C XXX KCMIL CU 320 MILS NL-EPR 25KV 133% INS LEVEL 25%TS GW 1 X X AWG CU MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL -- CSA 500 KCMIL CU 8.13mm (320 mils) NL-EPR 25KV 133% INS LEVEL 25%TS SR TC-ER 90{D}C FT4 -40{D}C LTGG {NESC}

Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Diameter Over Conductor | Diameter Over Insulation | Diameter Over Insulation Shield | Ground | Jacket Thickness ¹ | Approx. OD | Approx. Weight | Max Pull Tension | Min Bending Radius |
|--------------|------------|-------------------------|--------------------------|---------------------------------|-----------|-------------------------------|------------|----------------|------------------|--------------------|
| | AWG/ Kcmil | inch | inch | inch | No. x AWG | mil | inch | lb/1000ft | lb | inch |
| TBA | 1 | 0.322 | 0.999 | 1.059 | 1 x 4 | 110 | 2.579 | 3255 | 2009 | 18.1 |
| 647379 | 1/0 | 0.362 | 1.039 | 1.099 | 1 x 4 | 110 | 2.665 | 3586 | 2534 | 18.7 |
| TBA | 2/0 | 0.405 | 1.082 | 1.142 | 1 x 4 | 110 | 2.758 | 3979 | 3194 | 19.3 |
| TBA | 3/0 | 0.456 | 1.133 | 1.193 | 1 x 3 | 110 | 2.868 | 4503 | 4027 | 20.1 |
| TBA | 4/0 | 0.512 | 1.189 | 1.249 | 1 x 3 | 135 | 3.039 | 5234 | 5078 | 21.3 |
| 672603 | 250 | 0.542 | 1.228 | 1.288 | 1 x 2 | 135 | 3.110 | 5652 | 6000 | 22.1 |
| TBA | 350 | 0.661 | 1.347 | 1.407 | 1 x 2 | 135 | 3.380 | 7109 | 8400 | 23.7 |
| 679305 | 500 | 0.789 | 1.475 | 1.535 | 1 x 1 | 135 | 3.657 | 9012 | 12000 | 25.6 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

¹ Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 2 – Electrical and Engineering Data

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Shield Short Circuit Current 6 Cycles | Allowable Ampacity In Duct 90/105°C [†] | Allowable Ampacity In Air 90/105°C [‡] |
|------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|---------------------------------------|--|---|
| AWG/ Kcmil | Ω/1000ft | Ω/1000ft | MΩ*1000ft | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 1 | 0.129 | 0.161 | 0.061 | 0.049 | 0.522 + j0.334 | 0.162 + j0.049 | 3478 | 170/185 | 185/210 |
| 1/0 | 0.102 | 0.128 | 0.057 | 0.048 | 0.485 + j0.320 | 0.128 + j0.048 | 3608 | 195/210 | 215/240 |
| 2/0 | 0.081 | 0.101 | 0.053 | 0.046 | 0.455 + j0.306 | 0.102 + j0.046 | 3748 | 220/235 | 245/275 |
| 3/0 | 0.064 | 0.080 | 0.049 | 0.044 | 0.429 + j0.291 | 0.081 + j0.044 | 3914 | 250/270 | 285/315 |
| 4/0 | 0.051 | 0.064 | 0.045 | 0.043 | 0.407 + j0.275 | 0.065 + j0.043 | 4096 | 285/305 | 325/360 |
| 250 | 0.043 | 0.054 | 0.043 | 0.042 | 0.392 + j0.261 | 0.055 + j0.042 | 4275 | 310/335 | 360/400 |
| 350 | 0.031 | 0.039 | 0.038 | 0.039 | 0.366 + j0.238 | 0.040 + j0.039 | 4610 | 375/400 | 435/490 |
| 500 | 0.022 | 0.028 | 0.034 | 0.037 | 0.342 + j0.212 | 0.028 + j0.037 | 5026 | 450/485 | 535/600 |

* Calculations are based on 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

[†] Ampacities are based on TABLE 310.60(C)(79) Detail 1. of the 2020 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

[‡] Ampacities are based on TABLE 310.60(C)(71) of the 2020 National Electrical Code (40°C Ambient Air Temperature)

