

Armorlite® Type MC THHN/THWN Circuit Size Copper Conductor Oversized Neutral

Copper THHN/THWN Insulated Singles. Oversized Neutral Conductor. Green Insulated Ground. UL Listed 600 Volts Rated VW-1. Lightweight Aluminum Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid per ASTM B3 or Combination unilay-stranded copper conductors per ASTM B787
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Neutral:** Oversized insulated neutral with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
4. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
5. **Binder:** Mylar tape
6. **Armor:** Aluminum Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Cable Oversized-Neutral is suitable for use as follow:

- Applications affected by harmonics generated from non-linear switching loads, such as computers, variable frequency drives, electrical test equipment, and office equipment.
- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi- residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire Armorlite® Type MC Cable Oversized-Neutral meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify “Made in the USA Only!” when ordering to ensure your project receives American made products.
- REACH - European Community Regulation

SAMPLE PRINT LEGEND:

E96627 MASTER-DESIGN {UL} TYPE MC XX AWG THHN OR THWN CDRS WITH 2 X XX AWG NEUTRAL FOR USE IN CABLE TRAYS 600 VOLTS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Conductor Stranding	Insulation Thickness	Ground Size x Num	Neutral Size x Num	Diameter Over Armor	Overall Weight
	AWG/ Kcmil				mils	No. x AWG	No. x AWG	inch	lbs/1000ft
550654◇	12	3	BK/RD/GN	Solid	20	2 x 12	1 x 10	0.570	177
565760◇	12	4	BN/OE/ YW/GY	Solid	20	1 x 12	1 x 10	0.570	177
555209◇	12	6	See Table	Solid	20	2 x 12	3 x 10	0.667	284
690974◇	10	3	BK/RD/WE	Solid	25	1 x 10	1 x 8	0.656	219
691006◇	10	4	BK/RD/BE/ WE	Solid	25	1 x 10	1 x 8	0.704	269
552985◇	10	6	See Table	Solid	25	2 x 10	2 x 8	0.882	452
585022◇	10	8	See Table	Solid	25	1 x 10	2 x 8	0.907	492
552983◇	10	8	See Table	Solid	25	2 x 10	2 x 8	0.938	534
690826◇	12	2	BK/WE	19	20	1 x 12	1 x 10	0.509	122
551318◇	12	2	BK/WE	19	20	1 x 12	1 x 10	0.521	123
690859◇	12	3	BK/RD/WE	19	20	1 x 12	1 x 10	0.537	149
690883◇	12	4	BK/RD/BE/ WE	19	20	1 x 12	1 x 10	0.570	177
690917◇	12	4	BK/RD/BE/ WE	19	20	1 x 12	1 x 8	0.604	207
690941◇	12	5	See Table	19	20	1 x 12	1 x 10	0.606	203
551330◇	12	5	See Table	19	20	1 x 12	1 x 10	0.638	214
695130◇	12	6	See Table	19	20	2 x 12	2 x 10	0.654	270
553633◇	12	8	See Table	19	20	2 x 12	2 x 10	0.788	355

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Note: Conductor number = number of phase conductors plus neutral. Does not include green ground.



























































Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Allowable Ampacity Raceway 60°C [†]	Allowable Ampacity Raceway 75°C [†]	Allowable Ampacity Raceway 90°C [†]
	AWG/Kcmil	Inches	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
550654	12	3.9	1.662	2.002	20	25	30
565760	12	3.9	1.662	2.002	16	20	24
555209	12	4.6	1.662	2.002	16	20	24
690974	10	4.5	1.040	1.253	30	35	40
691006	10	4.9	1.040	1.253	24	28	32
552985	10	6.1	1.040	1.253	24	28	32
585022	10	6.3	1.040	1.253	21	24	28
552983	10	6.5	1.040	1.253	21	24	28
690826	12	3.5	1.662	2.002	20	25	30
551318	12	3.6	1.662	2.002	20	25	30
690859	12	3.7	1.662	2.002	20	25	30
690883	12	3.9	1.662	2.002	16	20	24
690917	12	4.2	1.662	2.002	16	20	24
690941	12	4.2	1.662	2.002	16	20	24
551330	12	4.4	1.662	2.002	16	20	24
695130	12	4.5	1.662	2.002	16	20	24
553633	12	5.5	1.662	2.002	14	17	21

[†] Ampacities have been adjusted for more than Three Current-Carrying Conductors

[†] Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

Color Table

Stock Number	Size AWG	Conductor Number	1	2	3	4	5	6	7	8	9	10
551330	12	5										
690941	12	5										
555209	12	6										
695130	12	6										
553633	12	8										
552985	10	6										
585022	10	6										
552983	10	8	