



Armorlite® Type MC THHN/THWN Circuit Size Copper Conductor Oversized Neutral

Copper THHN/THWN Insulated Singles. Oversized Neutral Conductor. Green Insulated Ground. UL Listed 600 Volts Rated VW-1. Lightweight Aluminum Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid per ASTM B3 or Combination unilay-stranded copper conductors per ASTM B787
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Neutral:** Oversized insulated neutral with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
4. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
5. **Binder:** Mylar tape
6. **Armor:** Aluminum Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Cable Oversized-Neutral is suitable for use as follow:

- Applications affected by harmonics generated from non-linear switching loads, such as computers, variable frequency drives, electrical test equipment, and office equipment.
- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi- residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire Armorlite® Type MC Cable Oversized-Neutral meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors





- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS WITH 2 X XX AWG NEUTRAL FOR USE IN CABLE TRAYS 600 VOLTS





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Num x Neutral Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AWG	No. x AWG	inch	lbs/1000ft	lbs/1000ft
12 AWG Solid											
550654◇	12	3	BK/RD/ GN	0.080	Solid	20	2x12	1x10	0.566	110	175
565760◇	12	4	BN/OE/ YW/GY	0.080	Solid	20	1x12	1x10	0.566	110	175
555209◇	12	6	See Table	0.080	Solid	20	2x12	3x10	0.663	192	282
10 AWG Solid											
690974◇	10	3	BK/RD/ WE	0.101	Solid	25	1x10	1x8	0.656	144	219
691006◇	10	4	BK/RD/ BE/WE	0.101	Solid	25	1x10	1x8	0.700	175	266
552985◇	10	6	See Table	0.101	Solid	25	2x10	2x8	0.878	288	448
585022◇	10	8	See Table	0.101	Solid	25	1x10	2x8	0.903	319	488
552983◇	10	8	See Table	0.101	Solid	25	2x10	2x8	0.934	350	529
12 AWG Solid											
690826◇	12	2	BK/WE	0.080	Solid	20	1x12	1x10	0.505	70	121
690859◇	12	3	BK/RD/ WE	0.080	Solid	20	1x12	1x10	0.533	90	147
690883◇	12	4	BK/RD/ BE/WE	0.080	Solid	20	1x12	1x10	0.566	110	175
690917◇	12	4	BK/RD/ BE/WE	0.080	Solid	20	1x12	1x8	0.600	131	205
690941◇	12	5	See Table	0.080	Solid	20	1x12	1x10	0.602	130	201
695130◇	12	6	See Table	0.080	Solid	20	2x12	2x10	0.650	182	268
553633◇	12	8	See Table	0.080	Solid	20	2x12	2x10	0.784	221	353
12 AWG 19 Strands											
551318◇	12	2	BK/WE	0.090	19	20	1x12	1x10	0.521	73	123
551330◇	12	5	See Table	0.090	19	20	1x12	1x10	0.634	132	212

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Note: Conductor number = number of phase conductors plus neutral. Does not include green ground.





Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
12 AWG Solid							
12	3	4.0	1.662	2.002	0.054	25	30
12	4	4.0	1.662	2.002	0.054	20	24
12	6	4.6	1.662	2.002	0.054	20	24
10 AWG Solid							
10	3	4.6	1.040	1.253	0.050	35	40
10	4	4.9	1.040	1.253	0.050	28	32
10	6	6.1	1.040	1.253	0.050	28	32
10	8	6.3	1.040	1.253	0.050	24	28
10	8	6.5	1.040	1.253	0.050	24	28
12 AWG Solid							
12	2	3.5	1.662	2.002	0.054	25	30
12	3	3.7	1.662	2.002	0.054	25	30
12	4	4.0	1.662	2.002	0.054	20	24
12	4	4.2	1.662	2.002	0.054	20	24
12	5	4.2	1.662	2.002	0.054	20	24
12	6	4.6	1.662	2.002	0.054	20	24
12	8	5.5	1.662	2.002	0.054	17	21
12 AWG 19 Strands							
12	2	3.6	1.662	2.002	0.054	25	30
12	5	4.4	1.662	2.002	0.054	20	24

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

Color Table

Stock Number	Size AWG	Conductor Number	1	2	3	4	5	6	7	8	9	10
551330	12	5	Black	Red	Blue	Orange	White	Green				
690941	12	5	Black	Red	Blue	Orange	White	Green				
555209	12	6	Black	Red	Blue	Orange	White	Green	White	Green	Green	
695130	12	6	Black	Red	Blue	Orange	White	Green	White	Green	Green	
553633	12	8	Black	Red	Blue	Orange	White	Green	White	Green	Green	Green
552985	10	6	Black	Red	Blue	Purple	White	Green	White	Green	Green	
585022	10	6	Black	Red	Blue	Orange	White	Green	White	Green	Green	
552983	10	8	Black	Red	Blue	Orange	White	Green	White	Green	Green	Green

