

HALO-FLEX™ CU 600/1000V XLPE Insulation Tape Shield Thermoplastic CPE-TP Jacket. XHHW-2 TC-ER-HL

Halo-Flex™ Type TC-ER-HL VFD Power Cable 600 or 1000 Volt Copper Conductors, Cross Linked Polyethylene (FR-XLPE) Insulation XHHW-2 -40°C Copper Tape Shield Thermoplastic CPE-TP Jacket, Control Cable Conductor Identification Method 3




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Flexible Stranded Rope-Lay Class I Copper per ASTM B172
- Insulation:** Fire Retardant Cross Linked Polyethylene (FR-XLPE) Type XHHW-2
- Ground:** Three symmetrical bare grounds flexible strand
- Filler:** Non-Hygroscopic flame retardant fillers
- Shield:** 25% overlap, helically applied copper tape shield. Optional braid shield for constructions up to 3C 4/0
- Rip Cord:** Rip cord for quick removal of extruded polymeric layer and jacket
- Extruded Polymeric Layer:** Extruded Polymeric Barrier Layer
- Overall Jacket:** Low-Friction SIM Technology® -40°C Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket

APPLICATIONS AND FEATURES:

Southwire's Halo-Flex™ 600V TC-ER-HL or 1000V TC-ER VFD power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. A gas/vapor-tight polymeric sheath is extruded over the core. Rated for use in Class I, II, or III, Division 1 & 2, Zone 1 & 2, hazardous locations per NEC Article 501, 502, and 503. Listed for exposed runs (TC-ER-HL) per NEC 336.10. - 40°C cold bend and cold impact. HALO-FLEX™ CPE jacket is made with patented SIM Technology. Cable can be installed in conduit without the aid of lubrication. PATENT www.patentsw.com. Shielded Halo-Flex™ cables can also be used for VFD (Variable Frequency Drive) applications where extra high frequencies are present.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1309 Marine Shipboard Cable (Optional)
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- UL 2225 Cables and Cable-Fittings For Use In Hazardous (Classified) Locations
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- RoHS-3 Complies with European Directive 2015/863
- ABS American Bureau of Shipping Approved

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE{R} HALO-FLEX{TM} VFD TC-ER-HL E75755 {UL} XX AWG CU 3 CDRS XHHW-2 GW 3 X XX AWG T/S XLPE/CPE 90{D}C JACKET 600V TYPE TC-ER-HL or 1000V TYPE TC-ER SUN. RES. FOR DIRECT BURIAL FT4 -40{D}C OIL RES I & II OR ABS RoHS-3 2015/863 COMPLIANT 07-KA180012-MSHA



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Diameter Over Insulation	Ground	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Min Bending Radius	Allowable Ampacity At 60°C	Allowable Ampacity 75°C	Allowable Ampacity 90°C
	AWG	No.	strands	inch	mil	inch	No. x AWG	mil	inch	lb / 1000ft	Ω /1000ft	Ω /1000ft	inch	Amp	Amp	Amp
4 AWG																
669548◇	4	3	112	0.235	47	0.329	3 x 12	84	1.033	865	0.274	0.357	12.4	70	85	95
2 AWG																
669554◇	2	3	168	0.315	47	0.409	3 x 10	84	1.162	1178	0.137	0.178	13.9	95	115	130
669560◇	1/0	3	259	0.385	58	0.501	3 x 10	84	1.404	1706	0.109	0.142	16.8	125	150	170
669566◇	2/0	3	324	0.420	58	0.536	3 x 10	84	1.497	2010	0.087	0.113	18.0	145	175	195
669572	3/0	3	418	0.470	58	0.586	3 x 8	84	1.588	2452	0.069	0.090	19.1	165	200	225
669578◇	4/0	3	532	0.535	55	0.645	3 x 8	116	1.779	3042	0.055	0.071	21.3	195	230	260
669593	250	3	627	0.605	65	0.735	3 x 8	116	1.974	3527	0.047	0.061	23.7	215	255	290
669584◇	350	3	855	0.670	65	0.800	3 x 6	116	2.146	4631	0.033	0.043	25.8	260	310	350
669587◇	500	3	1221	0.858	65	0.988	3 x 6	116	2.520	6279	0.023	0.036	30.2	320	380	430
669590	750	3	1850	1.094	80	1.254	3 x 4	147	3.157	9703	0.016	0.024	37.9	400	475	535

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

